

# SACB-4/ 8-M23 P12 - Distributor box



1491723

<https://www.phoenixcontact.com/ca/products/1491723>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, application: Standard, connection method: M12 socket / M12 PUSH-PULL female connector, number of slots: 4, number of positions: 5, coding: A, slot assignment: Double, status display: no, Universal; master cable connection: M23 plug-in connection (for standard and ONECLICK fast-locking system) 90°, shielding: no

## Your advantages

- Safety in the field, thanks to molded housing and high degree of protection
- Fast, secure installation of connectors with the push-pull fast-locking system in accordance with IEC 61076-2-010
- Save space: distributor box with double occupancy for two sensors in one slot

## Commercial data

Item number	1491723
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF3CBB
GTIN	4063151937164
Weight per piece (including packing)	201 g
Weight per piece (excluding packing)	197 g
Country of origin	DE

# SACB-4/ 8-M23 P12 - Distributor box



1491723

<https://www.phoenixcontact.com/ca/products/1491723>

## Technical data

### Notes

Assembly note	<b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
Note on application	Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories".
Note on application	An O-ring is required when using an M23 screw connector.

### Product properties

Product type	Distributor box
Application	Standard
Number of positions	5
Number of slots	4
Coding	A

### Electrical properties

Max. operating voltage $U_{max}$	135 V
Nominal voltage $U_N$	120 V AC
	120 V DC
Rated current, total	12 A
Max. current carrying capacity per path	2 A
Current carrying capacity per slot	4 A

### Connection data

#### Conductor connection

Sensor/actuator connection system	M12 socket
-----------------------------------	------------

#### Connection assignment

Slot/position = Wire color or connection	1 / 4 (A) = 15
	1 / 2 (B) = 7
	2 / 4 (A) = 5
	2 / 2 (B) = 4
	3 / 4 (A) = 16
	3 / 2 (B) = 8
	4 / 4 (A) = 3
	4 / 2 (B) = 14
	1-4 / 1 (+ 120 V) = 19
	1-4 / 3 (0 V) = 6
	1-4 / 5 (PE) = 12

### Signaling

# SACB-4/ 8-M23 P12 - Distributor box



1491723


<https://www.phoenixcontact.com/ca/products/1491723>

Status display present

no

## Dimensions

Dimensional drawing



Width

56 mm

Height

35.2 mm

Length

108 mm

## Material specifications

Material Housing

PBT

Flammability rating according to UL 94

V0

Seal material

FKM

Contact material

CuSn

Contact surface material

Ni/Au

Contact carrier material

PA

Material of contact, master cable side

CU alloy

Material of contact surface, master cable side

gold-plated

## Cable/line

Connection method

M23 plug-in connection (for standard and ONECLICK fast-locking system)

## Environmental and real-life conditions

Ambient conditions

Degree of protection

IP65

IP67

Ambient temperature (operation)

-25 °C ... 80 °C


# SACB-4/ 8-M23 P12 - Distributor box

1491723

<https://www.phoenixcontact.com/ca/products/1491723>

## Drawings


Dimensional drawing



1491723


<https://www.phoenixcontact.com/ca/products/1491723>

Schematic diagram



M12 slot, socket, 5-pos.

Schematic diagram




M23 plug connection pin, 19-pos.

# SACB-4/ 8-M23 P12 - Distributor box

1491723

<https://www.phoenixcontact.com/ca/products/1491723>

Circuit diagram



# SACB-4/ 8-M23 P12 - Distributor box



1491723

<https://www.phoenixcontact.com/ca/products/1491723>

## Classifications

### ECLASS

ECLASS-13.0	27440111
ECLASS-15.0	27440111

### ETIM

ETIM 9.0	EC003558
----------	----------

# SACB-4/ 8-M23 P12 - Distributor box



1491723

<https://www.phoenixcontact.com/ca/products/1491723>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
8240 Parkhill Drive  
Milton, Ontario L9T 5V7  
1-800-890-2820  
[cdinfo@phoenixcontact.ca](mailto:cdinfo@phoenixcontact.ca)