

CF FLASH 256MB PDPI BASIC - Memory



2700549

<https://www.phoenixcontact.com/us/products/2700549>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Program and configuration memory, plug-in, 256 MB with license key for licensing the PDPI - BASIC function block for precise multi-channel controllers with self-optimization, additional functions: e.g., for heating and cooling functions or hydraulic movements.

Product description

Program and configuration memory for storing application programs and other files in the file system of the PLC, with license key for the function block libraries.

The function blocks for the PDPI controllers from Phoenix Contact are licensed, i.e., a fee is charged for each controller on which blocks subject to a license are to be used. During runtime the blocks check the license stored in the controller and are then enabled or can be used for a limited time in demo mode.

Please observe the specified performance data of your controller(s) and check that they are suitable for your application.

For users who do not use the function block libraries, the program and configuration memory is also available without a license as an option.

Your advantages

- License key for licensing the PDPI - BASIC functional block
- For storing application programs and other files in the file system of the PLC
- Program and configuration memory, plug-in

Commercial data

Item number	2700549
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRAAZA
GTIN	4046356575782
Weight per piece (including packing)	17.1 g
Weight per piece (excluding packing)	15 g
Country of origin	DE

CF FLASH 256MB PDPI BASIC - Memory



2700549

<https://www.phoenixcontact.com/us/products/2700549>

Technical data

Product properties

Product type	Storage medium
Application	Multi-channel controller with self-optimization

Electrical properties

Maximum power dissipation for nominal condition	0.4 W
---	-------

Supply

Supply voltage	3.3 V DC
Supply voltage range	3.135 V DC ... 3.465 V DC
Typical current consumption	typ. 120 mA

Dimensions

Width	36.4 mm
Height	42.8 mm
Depth	3.3 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

CF FLASH 256MB PDPI BASIC - Memory



2700549

<https://www.phoenixcontact.com/us/products/2700549>

Classifications

ETIM

ETIM 8.0	EC000192
----------	----------

UNSPSC

UNSPSC 21.0	32101600
-------------	----------

CF FLASH 256MB PDPI BASIC - Memory



2700549
<https://www.phoenixcontact.com/us/products/2700549>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com