

BXT-4XP-SEC-T3-120+2X2-24AC - Surge protection device



2908686

<https://www.phoenixcontact.com/us/products/2908686>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wall-mounted NEMA 4/4X (IP66/67) polycarbonate enclosure with surge protection for 120 V AC/DC power and two 24 V AC loops with 28 V AC/40 V DC MCOV

Your advantages

- Eligible for limited lifetime warranty (in some U.S. markets)
- Customizable: expand base unit with SPDs to suit your application
- Polycarbonate and 316L stainless steel enclosures available
- UL 1449 Listed SPD
- Single solution for power, data, and signal in one enclosure

Commercial data

Item number	2908686
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL20
Product key	CL1481
GTIN	4055626321509
Weight per piece (including packing)	846 g
Weight per piece (excluding packing)	734 g
Country of origin	DE

BXT-4XP-SEC-T3-120+2X2-24AC - Surge protection device



2908686

<https://www.phoenixcontact.com/us/products/2908686>

Set consists of

PLT-SEC-T3-120-FM-UT - Type 3 surge protection device

2907918

<https://www.phoenixcontact.com/us/products/2907918>



Type 2/3 surge protection, consisting of protective plug and base element, with integrated status indicator and remote signaling for single-phase power supply networks. Nominal voltage: 120 V AC/DC

PT 2X2-24AC-ST - Surge protection plug

2838283

<https://www.phoenixcontact.com/us/products/2838283>



PT protective connector with protective circuit for two 2-wire floating signal circuits. 24 V AC nominal voltage. HART-compatible.

BXT-4XP-SEC-T3-120+2X2-24AC - Surge protection device




2908686

<https://www.phoenixcontact.com/us/products/2908686>

PT 2X2+F-BE - Surge protection base-element

2839224

<https://www.phoenixcontact.com/us/products/2839224>



Base element for protective plug PT with protective circuit for two 2-wire floating signal circuit, gas-filled surge arrester between the connections 3-4 (GND) and 9-10, for mounting on NS 35/7.5 and NS 35/15, housing width: 17.5 mm

BXT-4XP-SEC-T3-120+2X2-24AC - Surge protection device



2908686

<https://www.phoenixcontact.com/us/products/2908686>

Technical data

Product properties

Product type	Device protection
Type	DIN rail module, two-section, divisible
Surge protection fault message	optical
EN type	T2 / T3
Number of ports	One

Electrical properties

Nominal voltage U_N	120 V AC (Power)
	24 V AC (Signal)

Indicator/remote signaling

Connection name	Remote fault indicator contact
Switching function	Changeover contact

Connection data

Screw thread	M3
Tightening torque, min	0.5 Nm
Conductor cross-section flexible min.	0.2 mm ²
Conductor cross-section flexible max.	2.5 mm ²
Conductor cross-section, rigid min.	0.2 mm ²
Conductor cross-section, rigid max.	4 mm ²
Connection method	Screw connection
Screw thread	M3

Dimensions

Dimensional drawing	
Width	130 mm
Height	180 mm
Depth	120 mm

Material specifications

Housing material	PC
------------------	----

Protective circuit

Power supplies

Direction of action	L/N-PE & Signal Line-Shield-Earth Ground
---------------------	--

BXT-4XP-SEC-T3-120+2X2-24AC - Surge protection device



2908686

<https://www.phoenixcontact.com/us/products/2908686>

Nominal voltage U_N	120 V AC (TN-S)
	120 V AC (TT)

Information technology

Max. operating voltage U_{max}	150 V AC (Power)
	28 V AC (Signal)
Max. discharge current I_{max} (8/20) μ s	10 kA (Power)
Max. discharge current I_{max} (8/20) μ s maximum (line-line)	10 kA (Signal)
Max. discharge current I_{max} (8/20) μ s maximum (line-earth)	20 kA (Signal)
Resistance per path	2.2 Ω (Signal)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66/NEMA 4X
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	$\leq$ 2000 mm
Permissible humidity (operation)	5 % ... 95 %

Approvals

UL specifications

Maximum continuous operating voltage MCOV	150 V AC/DC
Short-circuit current rating (SCCR)	10 kA
Voltage protection rating VPR (L-N)	700 V
Voltage protection rating VPR (L-G)	1000 V
Voltage protection rating VPR (N-G)	900 V
Voltage protection rating VPR (DC+) - (DC-)	700 V
Voltage protection rating VPR (DC+) - G	1000 V
Voltage protection rating VPR (DC-) - G	900 V
UL type	type 2
Nominal discharge current I_n	5 kA
Maximum Circuit Breaker	25.00 A
Maximum Surge Current per Phase	20 A

Mounting

Mounting type	Panel mounting
---------------	----------------

BXT-4XP-SEC-T3-120+2X2-24AC - Surge protection device




2908686

<https://www.phoenixcontact.com/us/products/2908686>

Drawings

Dimensional drawing




BXT-4XP-SEC-T3-120+2X2-24AC - Surge protection device



2908686

<https://www.phoenixcontact.com/us/products/2908686>

Connection diagram



Connections for power protection only are shown. For signal protection connection, refer to included article datasheet. Signal and power protection may be bonded through DIN rail.

BXT-4XP-SEC-T3-120+2X2-24AC - Surge protection device



2908686

<https://www.phoenixcontact.com/us/products/2908686>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908686>



UL Listed

Approval ID: FILE E 330181



cUL Listed

Approval ID: FILE E 330181

2908686
<https://www.phoenixcontact.com/us/products/2908686>

Classifications

ECLASS

ECLASS-13.0	27171602
ECLASS-15.0	27171602

2908686
<https://www.phoenixcontact.com/us/products/2908686>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, Not qualified for the European market
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: n/a)

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com