

# MM-EML (EX12)R C1 YE/BK - Label



1118734

<https://www.phoenixcontact.com/us/products/1118734>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, yellow/black, unmarked, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, roll length: 8 m, text field height: 10 mm, text field width: 8000 mm

## Product description

The MM-EML... polyester self-adhesive labels are available as continuous media for equipment marking.

## Your advantages

- The material is cUL certified
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- The self-adhesive material in continuous format is particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application

## Commercial data

Item number	1118734
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG23
Product key	BG241E
GTIN	4063151047764
Weight per piece (including packing)	62 g
Weight per piece (excluding packing)	51 g
Customs tariff number	96121010
Country of origin	CN

## Technical data

### Product properties

Product type	Gerätemarker
--------------	--------------

### Marking

Identification technology	Thermal transfer
---------------------------	------------------

### Mounting

Mounting type	adhesive
---------------	----------

### Material specifications

Foil strength	50 µm
Adhesive	Acrylic
Color	multicolored
	yellow (RAL 1018)
	black (RAL 9005)
Material	Polyester
Components	free from silicone, halogen, and cadmium

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	24 months

### Dimensions

Length of roll	8.00 m
Height	12 mm
Depth	0.06 mm

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# MM-EML (EX12)R C1 YE/BK - Label



1118734

<https://www.phoenixcontact.com/us/products/1118734>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1118734>



**cULus Recognized**

Approval ID: MH48542

# MM-EML (EX12)R C1 YE/BK - Label



1118734

<https://www.phoenixcontact.com/us/products/1118734>

## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 9.0	EC001288
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# MM-EML (EX12)R C1 YE/BK - Label



1118734

<https://www.phoenixcontact.com/us/products/1118734>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)