

CATAN DOR6 UI8 - Relay module



1371364

<https://www.phoenixcontact.com/pc/products/1371364>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Extension module for Caton controller. 8 universal inputs and 6 digital outputs with bistable relays for 230 V AC/16 A. Local override operation via Caton Control Panel. Connection to the Caton controller via Single Pair Ethernet.

Product description

The CATAN DOR6 UI8 extension module is housed in a compact REG housing with an overall width of just 6 HP. It extends a Caton controller by eight additional universal inputs and six relay outputs for 230 V AC/16 A. The universal inputs are suitable for temperature sensors, 0 V ... 10 V interfaces or as meters, among other things. The bistable relays have contacts as N/C contacts and N/O contacts. They are designed for very high inrush currents.

Your advantages

- Space and cost savings thanks to highly flexible I/O configurability
- High-performance extension bus also enables distributed installation
- Startup and maintenance with plug-in display for local operation
- Power-saving bistable relays for high inrush currents
- Digital twin as the basis for smart buildings

Commercial data

Item number	1371364
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRHAFA
GTIN	4063151729950
Weight per piece (including packing)	292 g
Weight per piece (excluding packing)	270 g
Customs tariff number	85371098
Country of origin	DE

CATAN DOR6 UI8 - Relay module



1371364

<https://www.phoenixcontact.com/pc/products/1371364>

Technical data

Dimensions

Dimensions without display connected

Width	89.7 mm
Height	60.7 mm
Length	107.6 mm
Horizontal pitch	6 Div. (DIN rail housing in accordance with DIN 43871)

Dimensions with display connected

Width	89.7 mm
Height	68 mm
Length	107.6 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Interfaces

Extension bus (link bus)

Number of interfaces	2 (for extension modules)
Connection method	Push-in connection
Note on the connection method	Single Pair Ethernet (SPE) 10BASE-T1L, shielded
Transmission speed	10 Mbps
Transmission length	max. 350 m (between two devices)

Connection for Catan Control Panel

Number of interfaces	1
Connection method	USB 2.0 full speed, socket type C
Transmission speed	max. 12 Mbps

Input data

Analog: Universal input

Input name	Analog current inputs
Current input signal	0 mA ... 20 mA
	4 mA ... 20 mA
Protective circuit	Surge protection

Analog: Universal input

Input name	Analog voltage inputs
Voltage input signal	0 V ... 10 V
Input resistance of voltage input	> 5 MΩ
Protective circuit	Surge protection

CATAN DOR6 UI8 - Relay module



1371364

<https://www.phoenixcontact.com/pc/products/1371364>

Digital: Universal input

Input name	Digital inputs
Description of the input	EN 61131-2 type 2 and 3
Input voltage range "0" signal	-3 V DC ... 5 V DC (An open input always provides a 0 signal.)
Input voltage range "1" signal	11 V DC ... 30 V DC
Nominal input voltage U_{IN}	24 V DC

Digital: Universal input

Input name	Floating contacts
Input information	Connect the contact to ground.
Description of the input	Open/closed contact

Analog

Input name	Analog temperature inputs
Sensor types (RTD) that can be used	Pt 1000

Analog

Input name	Analog temperature inputs
Sensor types (RTD) that can be used	Ni 1000, LG-Ni 1000

Analog

Input name	Analog temperature inputs
Sensor types that can be used (TC)	NTC 10k, NTC 20k, NTC 10 k Pre

Analog

Input name	Analog resistance inputs
------------	--------------------------

Analog

Input name	Analog resistance inputs
------------	--------------------------

Counter: Universal input

Input name	Counter inputs
Input frequency	max. 20 Hz (Signal is debounced)
Resolution	1 Impulse

Output data

Relay

Number of outputs	6 (Changeover contact)
Connection method	Push-in connection
Switching voltage	max. 250 V
Switching capacity	max. 4000 VA
Limiting continuous current	16 A (Resistive load)
Mechanical service life	10 ⁶ cycles

Product properties

Product type	I/O component
--------------	---------------

CATAN DOR6 UI8 - Relay module



1371364

<https://www.phoenixcontact.com/pc/products/1371364>

Product family	Catan
Installation location	indoor use
Mounting position	horizontal
	Alternative mounting positions are possible, but can lead to a reduction in thermal performance.

Insulation characteristics

Overvoltage category	II (IEC 60664-1, EN 60664-1)
Pollution degree	2 (IEC 60664-1, EN 60664-1)

Electrical properties

Supply:

Designation	Supply
Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current consumption	max. 250 mA
	100 mA (without external load)
	150 mA (with display)

Electrical isolation/isolation of the voltage ranges

Test voltage: Extension bus/communications	500 V AC, 50 Hz, 1 min
Test voltage: Logic/functional ground	500 V AC, 50 Hz, 1 min
Test voltage: Relay contact / logic	4 kV AC, 50 Hz, 1 min
Test voltage: Relay contact / functional ground	4 kV AC, 50 Hz, 1 min
Test voltage: Relay contact/relay contact (open contact)	1 kV, 50 Hz, 1 min

Connection data

Connection technology

Connection name	Connections 1 ... 19 (relay)
-----------------	------------------------------

Connections 1 ... 19 (relay)

Connection method	Push-in connection
Conductor cross-section, flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 12
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 2.5 mm ²
Conductor cross-section flexible, with ferrule without plastic sleeve	0.25 mm ² ... 2.5 mm ²
Stripping length	10 mm
Conductor cross-section, rigid	0.2 mm ² ... 4 mm ² (Conductor connection with open terminal point)
	0.5 mm ² ... 4 mm ² (Push-in connection)
Nominal cross section	4 mm ²

Connections 31 ... 62 (power supply, link bus, universal inputs)

Connection method	Push-in connection
Conductor cross-section, flexible	0.5 mm ² ... 1.5 mm ²

CATAN DOR6 UI8 - Relay module



1371364

<https://www.phoenixcontact.com/pc/products/1371364>

Conductor cross-section AWG	24 ... 16
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 1.5 mm ²
Conductor cross-section flexible, with ferrule without plastic sleeve	0.25 mm ² ... 1.5 mm ²
Stripping length	10 mm
Conductor cross-section, rigid	0.2 mm ² ... 1.5 mm ² (Conductor connection with open terminal point)
	0.34 mm ² ... 1.5 mm ² (Push-in connection)
Nominal cross section	1.5 mm ²

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-5 °C ... 50 °C (up to 3000 m above mean sea level)
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	58 kPa ... 106 kPa (up to 4500 m above mean sea level)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

Mounting

Mounting type	DIN rail mounting (in accordance with DIN EN 60715)
Mounting position	horizontal

CATAN DOR6 UI8 - Relay module


1371364

<https://www.phoenixcontact.com/pc/products/1371364>




Drawings

Dimensional drawing



Dimensions

Block diagram



Internal wiring of the terminal points

CATAN DOR6 UI8 - Relay module



1371364

<https://www.phoenixcontact.com/pc/products/1371364>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/1371364>



cULus Listed

Approval ID: E238705

CATAN DOR6 UI8 - Relay module



1371364

<https://www.phoenixcontact.com/pc/products/1371364>

Classifications

ECLASS

ECLASS-13.0	27242604
ECLASS-15.0	27242604

ETIM

ETIM 9.0	EC001599
----------	----------

CATAN DOR6 UI8 - Relay module



1371364
<https://www.phoenixcontact.com/pc/products/1371364>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead titanium zirconium oxide(CAS: 12626-81-2)
	Lead(CAS: n/a)

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com