


# PT 1,5/S-QUATTRO BU - Feed-through terminal block



3208208

<https://www.phoenixcontact.com/us/products/3208208>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 500 V, nominal current: 17.5 A, number of connections: 4, connection method: Push-in connection, Rated cross section: 1.5 mm<sup>2</sup>, 1 level, cross section: 0.14 mm<sup>2</sup> - 1.5 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: blue

## Your advantages

- The compact design and front connection enable wiring in a confined space
- The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- In addition to the testing option in the double function shaft, all terminal blocks provide an additional test pick-off
- Tested for railway applications

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3208208       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE22          |
| Product key                          | BE2213        |
| GTIN                                 | 4046356564311 |
| Weight per piece (including packing) | 5.238 g       |
| Weight per piece (excluding packing) | 5.238 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | DE            |

# PT 1,5/S-QUATTRO BU - Feed-through terminal block



3208208

<https://www.phoenixcontact.com/us/products/3208208>

## Technical data

### Product properties

|                       |                                |
|-----------------------|--------------------------------|
| Product type          | Multi-conductor terminal block |
| Product family        | PT                             |
| Area of application   | Railway industry               |
|                       | Machine building               |
|                       | Plant engineering              |
| Number of connections | 4                              |
| Number of rows        | 1                              |
| Potentials            | 1                              |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                                                 |        |
|-------------------------------------------------|--------|
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 0.56 W |

### Connection data

|                                 |                     |
|---------------------------------|---------------------|
| Number of connections per level | 4                   |
| Nominal cross section           | 1.5 mm <sup>2</sup> |

#### 1 level

|                                                                   |                                                                                                            |
|-------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------|
| Connection method                                                 | Push-in connection                                                                                         |
| Stripping length                                                  | 8 mm ... 10 mm                                                                                             |
| Internal cylindrical gage                                         | A1 / B1                                                                                                    |
| Connection in acc. with standard                                  | IEC 60947-7-1                                                                                              |
| Conductor cross-section rigid                                     | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                                                               |
| Cross section AWG                                                 | 26 ... 16 (converted acc. to IEC)                                                                          |
| Conductor cross-section flexible                                  | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                                                               |
| Conductor cross-section, flexible [AWG]                           | 26 ... 16 (converted acc. to IEC)                                                                          |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                                                               |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.14 mm <sup>2</sup> ... 1 mm <sup>2</sup> Using the AI-S 1-8 TQ ferrule, Item No. 1200293, is recommended |
| Nominal current                                                   | 17.5 A                                                                                                     |
| Maximum load current                                              | 17.5 A                                                                                                     |
| Nominal voltage                                                   | 500 V                                                                                                      |
| Nominal cross section                                             | 1.5 mm <sup>2</sup>                                                                                        |

#### 1 level Connection cross sections directly pluggable

|                                                                   |                                              |
|-------------------------------------------------------------------|----------------------------------------------|
| Conductor cross-section rigid                                     | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.34 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.34 mm <sup>2</sup> ... 1 mm <sup>2</sup>   |

# PT 1,5/S-QUATTRO BU - Feed-through terminal block



3208208

<https://www.phoenixcontact.com/us/products/3208208>

## Ex data

### Rated data (ATEX/IECEx)

|                                                                          |                                       |
|--------------------------------------------------------------------------|---------------------------------------|
| Identification                                                           | Ex II 2 GD Ex eb IIC Gb               |
| Operating temperature range (1)                                          | -60 °C ... 85 °C                      |
| Operating temperature range (2)                                          | -40 °C ... 110 °C                     |
| Ex-certified accessories                                                 | 3208375 D-PT 1,5/S-QUATTRO            |
|                                                                          | 3030815 ATP-ST QUATTRO                |
|                                                                          | 1204504 SZF 0-0,4X2,5                 |
|                                                                          | 3022276 CLIPFIX 35-5                  |
|                                                                          | 3022218 CLIPFIX 35                    |
| List of bridges                                                          | Plug-in bridge / FBS 2-3,5 / 3213014  |
|                                                                          | Plug-in bridge / FBS 3-3,5 / 3213027  |
|                                                                          | Plug-in bridge / FBS 4-3,5 / 3213030  |
|                                                                          | Plug-in bridge / FBS 5-3,5 / 3213043  |
|                                                                          | Plug-in bridge / FBS 10-3,5 / 3213056 |
|                                                                          | Plug-in bridge / FBS 20-3,5 / 3213069 |
| Bridge data                                                              | 14.5 A (1.5 mm²)                      |
| Ex temperature increase                                                  | 40 K (15 A / 1.5 mm²)                 |
| for bridging with bridge                                                 | 352 V                                 |
| - At bridging between non-adjacent terminal blocks                       | 220 V                                 |
| - At bridging between non-adjacent terminal blocks via PE terminal block | 220 V                                 |
| - At cut-to-length bridging                                              | 166 V                                 |
| - At cut-to-length bridging with cover                                   | 275 V                                 |
| - At cut-to-length bridging with partition plate                         | 352 V                                 |
| Rated insulation voltage                                                 | 320 V                                 |
| output                                                                   | (Permanent)                           |

### Ex level General

|                      |        |
|----------------------|--------|
| Rated voltage        | 352 V  |
| Rated current        | 15 A   |
| Maximum load current | 15 A   |
| Contact resistance   | 1.5 mΩ |

### Ex connection data General

|                              |                      |
|------------------------------|----------------------|
| Nominal cross section        | 1.5 mm²              |
| Rated cross section AWG      | 16                   |
| Connection capacity rigid    | 0.14 mm² ... 1.5 mm² |
| Connection capacity AWG      | 26 ... 16            |
| Connection capacity flexible | 0.14 mm² ... 1.5 mm² |
| Connection capacity AWG      | 26 ... 16            |

## Dimensions

|       |        |
|-------|--------|
| Width | 3.5 mm |
|-------|--------|

# PT 1,5/S-QUATTRO BU - Feed-through terminal block



3208208

<https://www.phoenixcontact.com/us/products/3208208>

|                    |         |
|--------------------|---------|
| End cover width    | 2.2 mm  |
| Height             | 63.2 mm |
| Depth              | 30.5 mm |
| Depth on NS 35/7,5 | 32 mm   |
| Depth on NS 35/15  | 39.5 mm |

## Material specifications

|                                                                         |                 |
|-------------------------------------------------------------------------|-----------------|
| Color                                                                   | blue (RAL 5015) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group                                               | I               |
| Insulating material                                                     | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

### Ambient conditions

|                                          |                                                                                                                              |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)                                                    |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                                                                              |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                                                                              |
| Permissible humidity (operation)         | 20 % ... 90 %                                                                                                                |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                                                                                |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|---------------|-----------|

# PT 1,5/S-QUATTRO BU - Feed-through terminal block



3208208

<https://www.phoenixcontact.com/us/products/3208208>

|  |          |
|--|----------|
|  | NS 35/15 |
|--|----------|

## Drawings

Circuit diagram



# PT 1,5/S-QUATTRO BU - Feed-through terminal block



3208208

<https://www.phoenixcontact.com/us/products/3208208>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3208208>

|  <b>CSA</b><br>Approval ID: 2030668 |                       |                       |                   |                             |
|----------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                      | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                    | 300 V                 | 15 A                  | 26 - 14           | -                           |
| C                                                                                                                    | 300 V                 | 15 A                  | 26 - 14           | -                           |
| D                                                                                                                    | 600 V                 | 5 A                   | 26 - 14           | -                           |

|  <b>IECEE CB Scheme</b><br>Approval ID: DE1-62964 |                       |                       |                   |                             |
|------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                    | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                              | 500 V                 | -                     | -                 | 0.14 - 1.5                  |

|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                             |
|------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                    | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                                  | 300 V                 | 15 A                  | 26 - 14           | -                           |
| C                                                                                                                                  | 300 V                 | 15 A                  | 26 - 14           | -                           |
| D                                                                                                                                  | 600 V                 | 5 A                   | 26 - 14           | -                           |

|  <b>LR</b><br>Approval ID: LR2371832TA |  |  |  |  |
|---------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
|---------------------------------------------------------------------------------------------------------------------------|--|--|--|--|

|  <b>NK</b><br>Approval ID: 14ME0912 |  |  |  |  |
|------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
|------------------------------------------------------------------------------------------------------------------------|--|--|--|--|

|  <b>VDE Zeichengenehmigung</b><br>Approval ID: 40039739 |                       |                       |                   |                             |
|--------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                            | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                                      | 500 V                 | 17.5 A                | -                 | 0.14 - 1.5                  |

# PT 1,5/S-QUATTRO BU - Feed-through terminal block



3208208

<https://www.phoenixcontact.com/us/products/3208208>

## ABS

Approval ID: 21-2192245-PDA

## DNV

Approval ID: TAE000010T



## EAC Ex

Approval ID: RU C-DE.AB72.B.02351



## IECEx

Approval ID: IECEx SEV13.0005U



## ATEX

Approval ID: SEV13ATEX0159U



## CCC

Approval ID: 2020322313000631



## EAC Ex

Approval ID: KZ 7500525010101950



# PT 1,5/S-QUATTRO BU - Feed-through terminal block



3208208

<https://www.phoenixcontact.com/us/products/3208208>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
| ECLASS-15.0 | 27250101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PT 1,5/S-QUATTRO BU - Feed-through terminal block



3208208

<https://www.phoenixcontact.com/us/products/3208208>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)