

SACB-8/16-L-30,0PVC FB - Distributor box



1403355

<https://www.phoenixcontact.com/us/products/1403355>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, application: Food processing industry, connection method: M12 socket, number of slots: 8, number of positions: 5, status display: yes; master cable connection: Fixed connection, PVC, cable length: 30 m, shielding: no

Your advantages

- Safety in the field, thanks to molded housing and high degree of protection
- Convenient: increased machine availability thanks to quick and easy diagnostics
- Save space: distributor box with double occupancy for two sensors in one slot

Commercial data

Item number	1403355
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF44
Product key	AF3EAA
GTIN	4046356648950
Weight per piece (including packing)	7,347 g
Weight per piece (excluding packing)	7,347 g
Customs tariff number	85444290
Country of origin	DE

SACB-8/16-L-30,0PVC FB - Distributor box



1403355

<https://www.phoenixcontact.com/us/products/1403355>

Technical data

Notes

Assembly note	NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
Note on application	Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories".

Product properties

Product type	Distributor box
Application	Food processing industry
Number of positions	5
Number of slots	8

Electrical properties

Max. operating voltage U_{max}	30 V DC
Nominal voltage U_N	24 V DC
Rated current, total	12 A
Max. current carrying capacity per path	2 A
Current carrying capacity per slot	4 A

Connection data

Conductor connection

Sensor/actuator connection system	M12 socket
Tightening torque slot sensor/actuator cable	0.4 Nm

Signaling

Status display present	yes
------------------------	-----

Material specifications

Material Threaded sleeve	Stainless steel 1.4404
Material Housing	Stainless steel 1.4404
Material Molding compound	PUR
Seal material O-ring	FKM
Contact material	CuSn6
Contact surface material	gold-plated
Contact carrier material	PBT

Cable/line

Cable length	30 m
Connection method	Fixed connection
AWG signal line	20

SACB-8/16-L-30,0PVC FB - Distributor box



1403355

<https://www.phoenixcontact.com/us/products/1403355>

AWG power supply	17
------------------	----

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

SACB-8/16-L-30,0PVC FB - Distributor box




1403355

<https://www.phoenixcontact.com/us/products/1403355>


Drawings

Dimensional drawing




Dimensional drawing

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

Circuit diagram



SACB-8/16-L-30,0PVC FB - Distributor box



1403355

<https://www.phoenixcontact.com/us/products/1403355>

Classifications

ECLASS

ECLASS-13.0	27440108
-------------	----------

UNSPSC

UNSPSC 21.0	31251501
-------------	----------

SACB-8/16-L-30,0PVC FB - Distributor box



1403355

<https://www.phoenixcontact.com/us/products/1403355>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com