

SACC-E-MINM-3CON-NPT12-U50/1,0 - Flush-type connector



1417774

<https://www.phoenixcontact.com/us/products/1417774>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Flush-type connector, 3-position, Plug, straight, 7/8"-16UNF, on free cable end, Individual wires, cable length: 1 m, 2.50 mm², PVC litz wire

Commercial data

Item number	1417774
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF14
Product key	AF2ICA
GTIN	4055626403526
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85366990
Country of origin	MX

SACC-E-MINM-3CON-NPT12-U50/1,0 - Flush-type connector



1417774

<https://www.phoenixcontact.com/us/products/1417774>

Technical data

Notes

Trade restriction

CE note

The products are offered exclusively for export outside the EU and the European Economic Area.

Mounting

Tightening torque

10 lb_Fin.

1.12 Nm

Product properties

Product type

Circular connectors (device side)

Number of positions

3

No. of cable outlets

1

Shielded

no

Insulation characteristics

Degree of pollution

3

Material specifications

Flammability rating according to UL 94

V-0

Housing surface material

Al anodized

Contact material

Copper alloy

Contact surface material

Au

Contact carrier material

PVC

Material for screw connection

Anodized aluminum

Electrical properties

Insulation resistance

≥ 100 MΩ

Nominal voltage U_N

600 V AC/DC (UL rating)

50 V AC/DC (IEC rating)

Nominal current I_N

23.5 A (UL 2238)

7 A (UL 2237)

Connection data

Conductor connection

Connection method

Individual wires

Contact connection type

Pin

Conductor cross-section

2.5 mm²

Tightening torque

10 lb_Fin.

1.12 Nm

Mechanical properties

SACC-E-MINM-3CON-NPT12-U50/1,0 - Flush-type connector



1417774

<https://www.phoenixcontact.com/us/products/1417774>

Mechanical data

Insertion/withdrawal cycles	> 500
-----------------------------	-------

Connector

Connection 1

Head design	Plug
Head cable outlet	straight
Head thread type	7/8"-16UNF

Connection 2

Head design	free cable end
-------------	----------------

Cable/line

Cable length	1 m
Cable type	PVC litz wire
Wire diameter incl. insulation	4.5 mm
Single wire, color	green 1, black 2, white 3
Cable cross section	2.5 mm ²
AWG signal line	14
Material wire insulation	PVC
Thickness, insulation	Core insulation

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
	IP68
Ambient temperature (operation)	-20 °C ... 80 °C (Plug)
	-20 °C ... 80 °C (cable, fixed installation)

Standards and regulations

Standard designation	7/8" connector
Standards/specifications	UL 2237, UL 2238
Note	Suitable for use in Class I, Division 2 Groups A, B, C, D hazardous locations according to ISA standard 12.12.01-2015, section 8.2 and 8.8.3

SACC-E-MINM-3CON-NPT12-U50/1,0 - Flush-type connector




1417774

<https://www.phoenixcontact.com/us/products/1417774>


Drawings

Dimensional drawing



7/8" flush-type plug

Dimensional drawing



Housing cutout


SACC-E-MINM-3CON-NPT12-U50/1,0 - Flush-type connector



1417774


<https://www.phoenixcontact.com/us/products/1417774>

Schematic diagram



Pin assignment, plug, 7/8"-16UNF, 3-pos., view of male side (reference image)

Circuit diagram



Contact assignment of the 7/8" plug

SACC-E-MINM-3CON-NPT12-U50/1,0 - Flush-type connector



1417774

<https://www.phoenixcontact.com/us/products/1417774>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1417774>



UL Listed

Approval ID: FILE E 221474



cUL Listed

Approval ID: FILE E 221474



cUL Listed

Approval ID: FILE E 221474



UL Listed

Approval ID: FILE E 221474



cUL Listed

Approval ID: FILE E 468743



UL Listed

Approval ID: FILE E 468743

SACC-E-MINM-3CON-NPT12-U50/1,0 - Flush-type connector



1417774

<https://www.phoenixcontact.com/us/products/1417774>

Classifications

ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121413
-------------	----------

SACC-E-MINM-3CON-NPT12-U50/1,0 - Flush-type connector



1417774
<https://www.phoenixcontact.com/us/products/1417774>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com