

# SACC-CIP-M12MS-17P SMD SH-SP - Sample set



1418651

<https://www.phoenixcontact.com/us/products/1418651>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sample set, 17-position, Pin, straight, M12, A-coding, SMD reflow

## Commercial data

Item number	1418651
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	NULL
Product key	ABQXAA
GTIN	4055626163031
Weight per piece (including packing)	8.185 g
Weight per piece (excluding packing)	3.973 g
Customs tariff number	85366990
Country of origin	DE

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Number of positions	17
Seal present	yes
Shielded	yes
Coding	A
Thread type	M12

#### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	30 V
Nominal current $I_N$	1.5 A

### Connection data

Connection method	SMD reflow
-------------------	------------

### Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA

### Connector

#### Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	A

1418651

<https://www.phoenixcontact.com/us/products/1418651>

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection (not plugged in)	IP65 (not plugged in, by means of additional O-ring seal with device)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 105 °C
	-40 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations


Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

1418651

<https://www.phoenixcontact.com/us/products/1418651>

## Drawings

Schematic diagram



Pin assignment M12 male connector, 17-pos., male side view

# SACC-CIP-M12MS-17P SMD SH-SP - Sample set




1418651

<https://www.phoenixcontact.com/us/products/1418651>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1418651>

<div> <b>cULus Recognized</b> Approval ID: E221474-20160506</div>				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	30 V	1.5 A	-	-

# SACC-CIP-M12MS-17P SMD SH-SP - Sample set



1418651

<https://www.phoenixcontact.com/us/products/1418651>

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 9.0	EC003557
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1418651

<https://www.phoenixcontact.com/us/products/1418651>

## Environmental product compliance

## EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

## China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

## EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: n/a)
SCIP	f223d1b5-e5b7-4c4f-99fe-fdea327f65ce

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)