

EMT (15X4)R CUS - Insert label

0824375

<https://www.phoenixcontact.com/us/products/0824375>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insert label, can be ordered: by line, white, labeled according to customer specifications, cable diameter range: 0.6 ... 50 mm, mounting type: insert, text field height: 4 mm, text field width: 15 mm

Your advantages

- EMT ... insert labels for marking PATG and PATO marking sleeves for wire and cable identification
- Thanks to their special shape, EMT ... insert labels remain securely inside the collar once inserted
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Marking service: Phoenix Contact can custom-mark all EMT ... markers according to your requirements

Commercial data

Item number	0824375
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8121
GTIN	4046356352512
Weight per piece (including packing)	0.52 g
Weight per piece (excluding packing)	0.52 g
Country of origin	PL

EMT (15X4)R CUS - Insert label



0824375

<https://www.phoenixcontact.com/us/products/0824375>

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels per row	6
Identification technology	Thermal transfer for rolls

Dimensions

Width	15.00 mm
Height	4.00 mm
Depth	0.35 mm
Length	4 mm

Material specifications

Foil strength	125 µm
Color	white (RAL 9010)
Material	Polyester
Components	free from silicone and halogen

Cable/line

External cable diameter	0.6 mm ... 50 mm
-------------------------	------------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 200 °C (230 °C)	Test passed

EMT (15X4)R CUS - Insert label



0824375

<https://www.phoenixcontact.com/us/products/0824375>

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C / 50 % relative humidity
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	insert
---------------	--------

EMT (15X4)R CUS - Insert label



0824375

<https://www.phoenixcontact.com/us/products/0824375>

Classifications

ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

EMT (15X4)R CUS - Insert label



0824375

<https://www.phoenixcontact.com/us/products/0824375>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com