

1556702

https://www.phoenixcontact.com/us/products/1556702

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 8-position, PUR halogen-free, black-gray RAL 7021, shielded, Plug straight M12 SPEEDCON, coding: A, on Socket straight M12 SPEEDCON, coding: A, cable length: 3 m

Commercial data

Item number	1556702
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF03
Product key	AF1CMA
GTIN	4046356181372
Weight per piece (including packing)	189.9 g
Weight per piece (excluding packing)	189.9 g
Customs tariff number	85444290
Country of origin	PL



1556702

https://www.phoenixcontact.com/us/products/1556702

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	8
No. of cable outlets	1
Shielded	yes
Coding	A
Insulation characteristics	
Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	НВ
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	≥ 100 MΩ
Nominal voltage U _N	30 V AC
	30 V DC
Nominal current I _N	2 A

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Туре	Plug straight M12 SPEEDCON
Number of positions	8
Locking type	SPEEDCON
Coding type	A

Connection 2

Туре	Socket straight M12 SPEEDCON
Number of positions	8
Locking type	SPEEDCON
Coding type	A



1556702

https://www.phoenixcontact.com/us/products/1556702

Cable/line

Cable length	3 m
UR halogen-free black [PUR]	
Dimensional drawing	
Cable weight	53 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	8
Shielded	yes
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross section	8x 0.25 mm² (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.02 mm
External cable diameter	5.90 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, white, green, yellow, gray, pink, blue, red
Thickness, insulation	approx. 0.20 mm
Thickness, outer sheath	approx. 0.50 mm
Overall twist	8 wires around filler to the core
Optical shield covering	85 %
Max. conductor resistance	≤ 78 Ω/km (at 20 °C)
Insulation resistance	≥ 1 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V AC
Test voltage	≥ 3000 V AC (Spark test)
Test voltage Core/Shield	≥ 2000.00 V AC (for 60 s)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	59 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s²
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥1000000, Torsional



1556702

https://www.phoenixcontact.com/us/products/1556702

	frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
	according to IEC 60754-1
Flame resistance	in acc. with UL FT-2
	according to UL 758/1581 (horizontal)
	in accordance with UL 758/1581 FT2
	According to DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with IEC 60811-404
Other resistance	hydrolysis and microbe resistant
	Resistant to salt water
	low-abrasion
	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable
Ambient temperature (operation)	-40 °C 80 °C (cable, fixed installation)
	-25 °C 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C 90 °C (Plug / socket)
Ambient temperature (operation) (Cable, fixed installation)	-25 °C 80 °C (cable, fixed installation)
Ambient temperature (operation) (Cable, flexible installation)	-5 °C 80 °C (Cable, flexible installation)




1556702

https://www.phoenixcontact.com/us/products/1556702


Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing




M12 x 1 socket, straight, shielded



1556702


https://www.phoenixcontact.com/us/products/1556702





Pin assignment M12 plug, 8-pos., view plug side

Schematic diagram




Pin assignment M12 socket, 8-pos., A-coded, view female side



1556702

https://www.phoenixcontact.com/us/products/1556702

Circuit diagram



Contact assignment of M12 connector/socket



1556702

https://www.phoenixcontact.com/us/products/1556702

Classifications

ECLASS

ECLASS-13.0 27060311

Phoenix Contact 2025 © - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com