

RC-09S1N12T004 - Cable connector



1596207

<https://www.phoenixcontact.com/us/products/1596207>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M23, Cable connector, series: RC, angled, shielded: yes, Screw locking mechanism, No. of pos. : 8+1, Direction of rotation: Standard, contact connection type: Socket, Solder cup, cable diameter range: 7.5 mm ... 9.5 mm, coding: N



Commercial data

Item number	1596207
Packing unit	8 pc
Minimum order quantity	1 pc
Product key	ABRAFC
GTIN	4046356210157
Weight per piece (including packing)	146.21 g
Weight per piece (excluding packing)	139.921 g
Country of origin	DE

RC-09S1N12T004 - Cable connector



1596207

<https://www.phoenixcontact.com/us/products/1596207>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number Contact (Contact group 1)	1
Diameter Contact (Contact group 1)	2 mm
Litz wire cross-section min. Contact (Contact group 1)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 1)	2.5 mm ²
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number Contact (Contact group 2)	8
Diameter Contact (Contact group 2)	1 mm
Litz wire cross-section min. Contact (Contact group 2)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 2)	48 V AC
	48 V AC

Housing

Type	Cable connector housing
Thread type	M23
Design	angled
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn

RC-09S1N12T004 - Cable connector



1596207

<https://www.phoenixcontact.com/us/products/1596207>

Material (Rotating parts)	CuZn
Material (Housing surface)	Ni
Material (Seal)	FPM (O-ring)
Degree of protection (plugged in)	IP67

Seal

External cable diameter	7.5 mm ... 9.5 mm
-------------------------	-------------------


RC-09S1N12T004 - Cable connector

1596207

<https://www.phoenixcontact.com/us/products/1596207>

Drawings

Schematic diagram




Connector pin assignment

RC-09S1N12T004 - Cable connector

1596207

<https://www.phoenixcontact.com/us/products/1596207>

Schematic diagram




Connector pin assignment

RC-09S1N12T004 - Cable connector

1596207

<https://www.phoenixcontact.com/us/products/1596207>

Schematic diagram



Connector pin assignment


RC-09S1N12T004 - Cable connector



1596207

<https://www.phoenixcontact.com/us/products/1596207>

Schematic diagram



Dimensional drawing

RC-09S1N12T004 - Cable connector



1596207

<https://www.phoenixcontact.com/us/products/1596207>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-09S1N12T004 - Cable connector



1596207

<https://www.phoenixcontact.com/us/products/1596207>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: n/a)
SCIP	9b38bdf7-feff-4ec6-a98f-9d87c9476b45

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com