

# HC-B 6-EBUQ-2,5-OLOGO - Contact insert



1605561

<https://www.phoenixcontact.com/us/products/1605561>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Contact insert, size: B6, QUICKON connection, 500 V, 16 A, 0.34 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>



## Product description

### Contact insert

With QUICKON connection technology, the wires are connected with just a turn of the screwdriver. The wires do not have to be stripped first. This reduces connection time by at least 60%.

## Your advantages

- Shock and vibration-resistant in accordance with DIN EN 61373

## Commercial data

Item number	1605561
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	AF7ABC
GTIN	4017918940768
Weight per piece (including packing)	54.49 g
Weight per piece (excluding packing)	54.49 g
Country of origin	PL

# HC-B 6-EBUQ-2,5-OLOGO - Contact insert



1605561

<https://www.phoenixcontact.com/us/products/1605561>

## Technical data

### Notes

General	Connectors may be operated only when there is no load/voltage.
---------	--

### Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---

### Product properties

Product type	Contact insert with a fixed no. of positions
Type	B6
Number of positions	6

#### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Dimensions

#### Mechanical characteristics

Contact diameter	2.5 mm
------------------	--------

### Connection data

#### Connection technology

Connection technology	QUICKON connection
	QUICKON connection

#### Conductor connection

Conductor cross section	0.34 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Litz wire structure VDE 0295, Class 1 - 5/litz wire diameter $\geq$ 0.2 mm)
Connection cross section AWG	22 ... 14
Tightening torque	0.8 Nm ... 1.2 Nm (PE connection)
	0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the HEAVYCON housing)

### Electrical properties

Rated voltage (III/3)	500 V
	500 V
Rated surge voltage	6 kV
	6 kV
Rated current	16 A
	16 A

### Mechanical properties

# HC-B 6-EBUQ-2,5-OLOGO - Contact insert



1605561

<https://www.phoenixcontact.com/us/products/1605561>

## Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

## Material specifications

Flammability rating according to UL 94	V0
--	----

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

# HC-B 6-EBUQ-2,5-OLOGO - Contact insert


1605561

<https://www.phoenixcontact.com/us/products/1605561>




## Drawings

Dimensional drawing




## Female insert


Dimensional drawing



Mounting cutout when used without housing



Derating diagram for flexible conductors



Derating diagram for solid conductors

# HC-B 6-EBUQ-2,5-OLOGO - Contact insert



1605561

<https://www.phoenixcontact.com/us/products/1605561>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1605561>



**EAC**

Approval ID: RU C-DE.AI30.B.01102

# HC-B 6-EBUQ-2,5-OLOGO - Contact insert



1605561

<https://www.phoenixcontact.com/us/products/1605561>

## Classifications

### ECLASS

ECLASS-13.0	27440205
ECLASS-15.0	27440205

### ETIM

ETIM 9.0	EC000438
----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# HC-B 6-EBUQ-2,5-OLOGO - Contact insert



1605561  
<https://www.phoenixcontact.com/us/products/1605561>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)