

# MM-WMTB HF (55X15)R C1 YE/BK - Cable marker



1116208

<https://www.phoenixcontact.com/us/products/1116208>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Roll, yellow/black, unmarked, can be labeled with: THERMOMARK GO, cable diameter range: 6 ... 115 mm, mounting type: Assembly with cable ties, Number of individual labels: 20, text field height: 13.4 mm, text field width: 55 mm

## Product description

Prepunched, halogen-free MM-WMTB HF conductor markers made of polyurethane are attached to the conductor with a cable tie.

## Your advantages

- The pre-punched geometry enables easy and convenient use
- Thanks to the innovative material composition, each label can be printed which results in zero wastage
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- No visible difference between retrospective marking and existing markings created with a desktop roll printer
- The cable markers are mounted very easily using a cable tie. Alternatively, a large number of conductors can also be bundled together in this way
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1116208       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BG23          |
| Product key                          | BG221E        |
| GTIN                                 | 4063151042110 |
| Weight per piece (including packing) | 82 g          |
| Weight per piece (excluding packing) | 78.8 g        |
| Customs tariff number                | 96121010      |
| Country of origin                    | CN            |

# MM-WMTB HF (55X15)R C1 YE/BK - Cable marker



1116208

<https://www.phoenixcontact.com/us/products/1116208>

## Technical data

### Product properties

|              |                  |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

### Marking

|                                     |                  |
|-------------------------------------|------------------|
| Number of individual labels         | 20               |
| Number of individual labels per row | 1                |
| Identification technology           | Thermal transfer |

### Dimensions

|        |         |
|--------|---------|
| Width  | 75 mm   |
| Height | 14.4 mm |
| Depth  | 0.45 mm |

### Material specifications

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Foil strength                          | 450 µm                                   |
| Color                                  | multicolored                             |
|                                        | yellow (RAL 1018)                        |
|                                        | black (RAL 9005)                         |
| Material                               | PUR                                      |
| Flammability rating according to UL 94 | HB                                       |
| Components                             | free from silicone, halogen, and cadmium |

### Cable/line

|                         |                 |
|-------------------------|-----------------|
| External cable diameter | 6 mm ... 115 mm |
|-------------------------|-----------------|

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### Test for substances that would hinder coating with paint or varnish

|               |                                       |
|---------------|---------------------------------------|
| Result        | Test passed                           |
| Specification | DIN EN ISO 1518-1:2019-10 (following) |
| Requirements  | ≥ 5 N                                 |
| Result        | Test passed                           |

#### Tesafilm test

|               |                                  |
|---------------|----------------------------------|
| Specification | DIN EN ISO 2409:2013 (following) |
| Result        | Test passed                      |

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |

# MM-WMTB HF (55X15)R C1 YE/BK - Cable marker



1116208

<https://www.phoenixcontact.com/us/products/1116208>

|           |                         |
|-----------|-------------------------|
| Procedure | Artificial irradiation. |
|-----------|-------------------------|

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 100 °C (121 °C) | Test passed                     |

## Wipe resistance of inscriptions

|                                                   |                                                                                        |
|---------------------------------------------------|----------------------------------------------------------------------------------------|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0]                    | Test passed                                                                            |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed                                                                            |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed                                                                            |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                                                            |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                                                            |
| Specification                                     | ISO 175:2010 (following)                                                               |
| Test duration                                     | 168 h                                                                                  |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                                                            |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                                                            |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed                                                                            |
| IRM 901                                           | Test passed                                                                            |
| IRM 902                                           | Test passed                                                                            |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |
| Test duration | 96 h                      |

## Ambient conditions

|                                                     |                                                                                 |
|-----------------------------------------------------|---------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -25 °C ... 80 °C                                                                |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                           |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life                                          | 24 months                                                                       |

# MM-WMTB HF (55X15)R C1 YE/BK - Cable marker



1116208

<https://www.phoenixcontact.com/us/products/1116208>

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Mounting

|               |                          |
|---------------|--------------------------|
| Mounting type | Assembly with cable ties |
|---------------|--------------------------|

# MM-WMTB HF (55X15)R C1 YE/BK - Cable marker



1116208

<https://www.phoenixcontact.com/us/products/1116208>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001530 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# MM-WMTB HF (55X15)R C1 YE/BK - Cable marker



1116208

<https://www.phoenixcontact.com/us/products/1116208>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)