

VS-09-BU-DSUB-CD-B - D-SUB contact support



1688861

<https://www.phoenixcontact.com/us/products/1688861>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact carrier, shell size 1, for nine signal contacts, type of contact socket, for crimp contacts, straight, fixing with a 3 mm hole, for panel mounting frame and sleeve housing VS-09-..



Your advantages

- D-SUB 9 connection
- Compatible with IP67 sleeve housing and panel-mount frame
- Easy assembly

Commercial data

Item number	1688861
Packing unit	100 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAB
GTIN	4017918822996
Weight per piece (including packing)	6.053 g
Weight per piece (excluding packing)	4.87 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

General	Test voltage only in combination with crimp contact, Item No.: 1418788.
---------	---

Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	9
Connection profile	D-SUB
Number of slots	1
Shielded	yes

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated voltage in acc. with IEC 61076-2-101	400 V
Rated voltage (III/3)	125 V
Rated surge voltage	1 kV
Rated current	5 A (at 20 °C)
Test voltage	1500 V
Transmission medium	Copper

Connection data

Connection method	Crimp connection
-------------------	------------------

Dimensions

Width	17.9 mm
Height	12.93 mm
Length	31.19 mm

Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact surface material	Gold
Contact carrier material	Glass-fiber reinforced thermoplastics, UL 94 V0

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

VS-09-BU-DSUB-CD-B - D-SUB contact support



1688861

<https://www.phoenixcontact.com/us/products/1688861>

Insertion force per signal contact	$\leq 3.40 \text{ N}$
------------------------------------	-----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 130 °C

Mounting

Mounting type	Screw mounting
---------------	----------------

VS-09-BU-DSUB-CD-B - D-SUB contact support



1688861

<https://www.phoenixcontact.com/us/products/1688861>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1688861>



UL Recognized

Approval ID: E118976

1688861

<https://www.phoenixcontact.com/us/products/1688861>

Classifications

ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

ETIM

ETIM 9.0	EC001132
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------



1688861

<https://www.phoenixcontact.com/us/products/1688861>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com