

1702774

https://www.phoenixcontact.com/us/products/1702774

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, Range of articles: SUNCLIX, housing material: PPE, color: black, min. conductor cross-section: 4 mm², rated current: 40 A, Connection method: Crimp, cable length: 100

Commercial data

Item number	1702774
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	ABMBFA
GTIN	4046356617499
Weight per piece (including packing)	39.4 g
Weight per piece (excluding packing)	39.4 g
Country of origin	DE



1702774

https://www.phoenixcontact.com/us/products/1702774

Technical data

Notes

Safety note

Safety note

- WARNING: Commission properly functioning products only.
 The products must be regularly inspected for damage.
 Decommission defective products immediately. Replace damaged products. Repairs are not possible.
- WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.

WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.

- The products are suitable for applications in plant, controller, and electrical device engineering.
- Assembled products may not be manipulated or improperly opened.
- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).
- When using the product in direct connection with third-party manufacturers, the user is responsible.
- For operating voltages > 50 V AC, conductive connector housings must be grounded
- Ensure that the protective or functional ground has been properly connected.
- Observe the corresponding technical data. You will find information:
- o On the product
- o On the packing label
- o In the supplied documentation
- o Online at phoenixcontact.com/products under the product
- The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.
- Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at phoenixcontact.com/products
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
- Operate the connector only when it is fully plugged in and interlocked.
- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.



1702774

https://www.phoenixcontact.com/us/products/1702774

	Observe the minimum bending radius of the cable. Lay the cable without twisting it.
roduct properties	
Product type	Panel feed-through
Product family	SUNCLIX
Insulation characteristics	
Protection class	II .
Degree of pollution	2
onnection data	
Conductor connection	
Tightening torque	1.8 Nm ±0.1 Nm
imensions	
Dimensional drawing	11.6 10.6
Width	26.3 mm
Height	26.3 mm
Length	41.5 mm
ectrical properties	
Rated voltage (II/2)	1000 V
Rated voltage (III/2)	1500 V
Rated surge voltage (II/2)	8 kV
Rated surge voltage (III/2)	8 kV
Rated surge voltage (III/3)	16 kV
Rated current (4.0 mm²)	40 A
Contact resistance	0.45 mΩ
echanical properties	
Mechanical data	
Insertion force	45 N ±10 N
Withdrawal force	250 N ±50 N
aterial specifications	
Color	black
Color of the housing part	black
Flammability rating according to UL 94	V0
Insulating material group	I / CTI 600



1702774

https://www.phoenixcontact.com/us/products/1702774

Seal material	EPDM
Insulating material	mPPE
Contact surface	Silver Ag
Housing material	PPE
Cable seal material	Elastosil
Contact material	Cu
Contact surface material	Ag
Contact carrier material	PPE
Outer sheath, material	PE-X

Cable/line

Cable length	100 mm
Cable type	S02
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	56x0.3
External cable diameter	4.60 mm ±0.15 mm
Outer sheath, material	PE-X
External sheath, color	red
Single wire, cross section	4 mm²
Smallest bending radius, fixed installation	23 mm
Smallest bending radius, movable installation	46 mm
Cable pull-out force	> 80 N
Halogen-free	yes

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP66/IP68 (2 m / 24 h)
Degree of protection (not plugged in)	IP65
Ambient temperature (operation)	-40 °C 85 °C
Ambient temperature (assembly)	-25 °C 50 °C



1702774

https://www.phoenixcontact.com/us/products/1702774

Drawings

18,6

Dimension x = cable length c: panel thickness - plastic: 2 - 6 mm; metal: 2 - 5 mm


41,6 C DO NOT DISCONNECT UNDER LOAD



1702774

https://www.phoenixcontact.com/us/products/1702774

Dimensional drawing





1702774

https://www.phoenixcontact.com/us/products/1702774

Classifications

ETIM 8.0	EC002635	
UNSPSC		
UNSPSC 21.0	39121400	



1702774

https://www.phoenixcontact.com/us/products/1702774

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com