

SACB-SH-8 PARA VA - Distributor box



1401261

<https://www.phoenixcontact.com/us/products/1401261>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, connection method: M12 socket Stainless steel, number of slots: 8, number of positions: 5, coding: A, slot assignment: parallel, status display: no, Universal, shielding: yes

Commercial data

Item number	1401261
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF3EAA
GTIN	4046356546232
Weight per piece (including packing)	525 g
Weight per piece (excluding packing)	525 g
Country of origin	DE

SACB-SH-8 PARA VA - Distributor box



1401261
<https://www.phoenixcontact.com/us/products/1401261>

Technical data

Notes

Assembly note	NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
Note on application	Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories".

Product properties

Product type	Distributor box
Number of positions	5
Number of slots	8
Coding	A

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC
Rated current, total	4 A
Max. current carrying capacity per path	2 A
Current carrying capacity per slot	4 A

Connection data

Conductor connection		
Sensor/actuator connection system	M12 socket	
Tightening torque slot sensor/actuator cable	0.4 Nm	

Signaling

Status display present	no
------------------------	----

Dimensions

Dimensional drawing	
Width	60 mm
Height	35 mm
Length	170 mm

Material specifications

Material Threaded sleeve	Stainless steel 1.4404
--------------------------	------------------------

SACB-SH-8 PARA VA - Distributor box



1401261

<https://www.phoenixcontact.com/us/products/1401261>

Material Housing	Stainless steel 1.4404
Material Molding compound	PUR
Flammability rating according to UL 94	V0
Seal material O-ring	FKM
Contact material	CuSn6
Contact surface material	gold-plated
Contact carrier material	PBT

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-30 °C ... 80 °C

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

SACB-SH-8 PARA VA - Distributor box




1401261

<https://www.phoenixcontact.com/us/products/1401261>

Drawings

Dimensional drawing




SACB-SH-8 PARA VA - Distributor box

1401261


<https://www.phoenixcontact.com/us/products/1401261>

Schematic diagram



M12 slot, socket, 5-pos.

Circuit diagram



SACB-SH-8 PARA VA - Distributor box



1401261

<https://www.phoenixcontact.com/us/products/1401261>

Classifications

ECLASS

ECLASS-13.0	27440111
ECLASS-15.0	27440111

ETIM

ETIM 9.0	EC003558
----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SACB-SH-8 PARA VA - Distributor box



1401261
<https://www.phoenixcontact.com/us/products/1401261>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com