

SAC-8P-M12MS/1-PVC/FS SHOBS VA - Sensor/actuator cable



1404881
<https://www.phoenixcontact.com/us/products/1404881>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 8-pos., PVC, RAL 9005 (black), shielded, straight M12 male plug, A-coded, to straight M12 female plug, A-coded, cable length: 1 m, with VA knurl

Commercial data

Item number	1404881
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CMA
GTIN	4046356726894
Weight per piece (including packing)	123.4 g
Weight per piece (excluding packing)	121 g
Country of origin	PL

SAC-8P-M12MS/1-PVC/FS SHOBS VA - Sensor/actuator cable



1404881

<https://www.phoenixcontact.com/us/products/1404881>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	8
No. of cable outlets	1
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Stainless steel

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V AC
	30 V DC
Nominal current I_N	2 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Plug straight M12
Number of positions	8
Coding type	A

Connection 2

SAC-8P-M12MS/1-PVC/FS SHOBS VA - Sensor/actuator cable




1404881

<https://www.phoenixcontact.com/us/products/1404881>

Type	Socket straight M12
Number of positions	8
Coding type	A

Cable/line

PVC black [PVC]

Dimensional drawing	
Note	The cable is not suitable for use with drag chains.
Cable weight	85 kg/km
UL AWM Style	2517
Number of positions	8
Shielded	yes
Cable type	PVC black [PVC]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross section	8x 0.25 mm ² (Signal line)
Wire diameter incl. insulation	1.5 mm ±0.05 mm (Signal line)
External cable diameter	7.70 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material, filler	PVC
Material wire insulation	PVC
Single wire, color	white, brown, green, yellow, gray, pink, blue, red
Thickness, insulation	≥ 0.38 mm (Conductor insulation, signal line) ≥ 0.76 mm (Outer cable sheath)
Overall twist	8 wires around filler to the core, twisted in with additional Cu litz in the wire outer godet
Optical shield covering	85 %
Max. conductor resistance	≤ 78 Ω/km
Insulation resistance	≥ 10 GΩ*km
Nominal voltage, cable	300 V
Test voltage	3000 V
Smallest bending radius, fixed installation	38.5 mm
Smallest bending radius, movable installation	77 mm

SAC-8P-M12MS/1-PVC/FS SHOBS VA - Sensor/actuator cable



1404881

<https://www.phoenixcontact.com/us/products/1404881>

Flame resistance	According to UL 758/1581 (Cable Flame)
	According to DIN EN 60332-1-2 (60 s)
Resistance to oil	According to DIN EN 60811-2-1, 168 h at 80°C
Ambient temperature (operation)	-25 °C ... 105 °C (cable, fixed installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
	IP69K


SAC-8P-M12MS/1-PVC/FS SHOBS VA - Sensor/actuator cable

1404881

<https://www.phoenixcontact.com/us/products/1404881>


Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing




M12 x 1 socket, straight, shielded

SAC-8P-M12MS/1-PVC/FS SHOBS VA - Sensor/actuator cable

1404881


<https://www.phoenixcontact.com/us/products/1404881>

Schematic diagram



Pin assignment M12 plug, 8-pos., view plug side

Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side

SAC-8P-M12MS/1-PVC/FS SHOBS VA - Sensor/actuator cable



1404881

<https://www.phoenixcontact.com/us/products/1404881>

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

SAC-8P-M12MS/1-PVC/FS SHOBS VA - Sensor/actuator cable



1404881
<https://www.phoenixcontact.com/us/products/1404881>

Classifications

ECLASS

ECLASS-13.0	27060311
-------------	----------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com