

1456556

https://www.phoenixcontact.com/us/products/1456556

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 4-position, Pin, straight, M12-SPEEDCON, D-coding, Wave soldering, this item is expected to be lead-free from Q1 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- · All standard pin assignments and codings for signal, data, and power transmission with a uniform design-in design
- · For high transmission reliability: optional shield connection to the housing by means of shield contact

Commercial data

Item number	1456556
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB26
Product key	ABQEGB
GTIN	4046356617116
Weight per piece (including packing)	14.2 g
Weight per piece (excluding packing)	12.941 g
Customs tariff number	85366990
Country of origin	DE



1456556

https://www.phoenixcontact.com/us/products/1456556

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	Lock nut is included in the scope of delivery

Mounting

Mounting type	Rear mounting (M16 x 1,5)
Tightening torque	3 Nm 4 Nm (Installation-side)

Product properties

Product type	Circular connectors (device side)
Application	Data
Number of positions	4
No. of cable outlets	1
Shielded	yes
Coding	D
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Dimensions

Length of the solder pin	6 mm
	6 mm

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Insulating body	PA 6.6
Material Contact	CuZn
Material Contact surface	Ni/Au
Material Seal	NBR
Flammability rating according to UL 94	V0
Contact carrier color	green

Electrical properties

Rated surge voltage	2.5 kV



1456556

https://www.phoenixcontact.com/us/products/1456556

Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Nominal voltage U _N	250 V
Nominal current I _N	4 A

Connection data

Conductor connection

Connection method	Wave soldering
Contact connection type	Pin
Tightening torque	3 Nm 4 Nm (Installation-side)

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	D

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
Ambient temperature (operation) (fixed installation)	-40 °C 70 °C (Plug / socket)
Ambient temperature (operation) (flexible installation)	-50 °C 70 °C (Cable, flexible installation)
Ambient temperature (operation) (male connector/female connector)	-20 °C 60 °C (cable, fixed installation)

Standards and regulations


Standard designation	M12 circular connector	
Standards/specifications	according to IEC 61076-2-101	



1456556

https://www.phoenixcontact.com/us/products/1456556

Drawings



Pin assignment M12 male connector, 4-pos., D-coded, male side



1456556

https://www.phoenixcontact.com/us/products/1456556

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1456556

71	UL Recognized Approval ID: E118976-20100522				
		Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine					
		250 V	4 A	22	-

c 711 vs	cULus Recognized Approval ID: E221474-20140616			
	Nominal voltage U_N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	250 V	4 A	-	-



1456556

https://www.phoenixcontact.com/us/products/1456556

Classifications

ECLASS

	ECLASS-13.0	27440110
	ECLASS-15.0	27440110
E 1	ГІМ	
	IIVI	
	ETIM 9.0	EC003568
1 11	NSPSC	
UI	NOFOC	
	UNSPSC 21.0	39121400



1456556

https://www.phoenixcontact.com/us/products/1456556

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ce42acb9-dad7-4d81-bbe3-becd6ef09122

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com