

# CA-12P1N126L00 - Device connector front mounting



1624050

<https://www.phoenixcontact.com/us/products/1624050>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Pin, Solder cup, Axial seal, coding: N, this item is expected to be lead-free from Q1 2027 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

## Commercial data

Item number	1624050
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAEL
GTIN	4055626227719
Weight per piece (including packing)	42.2 g
Weight per piece (excluding packing)	34.019 g
Customs tariff number	85366990
Country of origin	DE

# CA-12P1N126L00 - Device connector front mounting



1624050

<https://www.phoenixcontact.com/us/products/1624050>

## Technical data

### Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

### Material specifications

Flammability rating according to UL 94	V0
----------------------------------------	----

### Connector

#### Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Number Contact (Contact group 1)	0
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number Contact (Contact group 2)	12
Diameter Contact (Contact group 2)	1 mm
Litz wire cross-section max. Contact (Contact group 2)	1 mm <sup>2</sup>
Rated current Contact (Contact group 2)	8 A

#### Housing

Thread type	M23
Design	straight
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Mounting type	Front mounting (M20 x 1,5)
Assembly note	Central fastening
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Degree of protection (plugged in)	IP67
Seal for the device	Axial seal

# CA-12P1N126L00 - Device connector front mounting



1624050

<https://www.phoenixcontact.com/us/products/1624050>

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)
---------------------------------



-40 °C ... 125 °C
-------------------

1624050

<https://www.phoenixcontact.com/us/products/1624050>



## Drawings

Dimensional drawing




Installation dimensions

Dimensional drawing




Installation dimensions

Schematic diagram



Connector pin assignment

Schematic diagram




Connector pin assignment


1624050

<https://www.phoenixcontact.com/us/products/1624050>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1624050>

<div> <b>cUL Recognized</b> Approval ID: E335019-20141210</div>				
	Nominal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>
keine				
	48 V	6 A	18	-

<div> <b>UL Recognized</b> Approval ID: E335019-20141210</div>				
	Nominal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>
keine				
	48 V	8 A	18	-

# CA-12P1N126L00 - Device connector front mounting



1624050

<https://www.phoenixcontact.com/us/products/1624050>

## Classifications

### ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

### ETIM

ETIM 9.0	EC003569
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------



# CA-12P1N126L00 - Device connector front mounting



1624050

<https://www.phoenixcontact.com/us/products/1624050>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e43364eb-1746-44db-a574-f2b783aa706d

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)