

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Housing half shell (left), tall design, width: 6.3 mm, height: 99 mm, depth: 112.85 mm, color: gray (similar RAL 7042)

Your advantages

- Easy installation
- Variety of connection technology

Commercial data

Item number	2202156
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	ACHABZ
GTIN	4055626004259
Weight per piece (including packing)	19.23 g
Weight per piece (excluding packing)	19.408 g
Country of origin	DE

# ME MAX GEH-L G 2-2 GY - Housing half shell



2202156

<https://www.phoenixcontact.com/us/products/2202156>

## Technical data


### Notes

Assembly note	Please observe the application note in the download area.
Recommendation	Material of contact pads for bus connector, galvanic gold (hard gold)

### Product properties

Product type	Housing half shells
Housing type	DIN rail housing
Housing series	ME-MAX

### Dimensions

Dimensional drawing	
	
Width	6.3 mm
Height	99 mm
Depth	112.85 mm
Depth from top edge of DIN rail	107 mm

### PCB design

PCB thickness	1.4 mm ... 1.8 mm
---------------	-------------------

### Material specifications

Color (Housing)	gray (RAL 7042)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Housing material	PA
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

# ME MAX GEH-L G 2-2 GY - Housing half shell



2202156

<https://www.phoenixcontact.com/us/products/2202156>

## PCB data

Type of PCB mount	Latching
Thickness of the PCB	1.4 mm ... 1.8 mm

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# ME MAX GEH-L G 2-2 GY - Housing half shell


2202156

<https://www.phoenixcontact.com/us/products/2202156>



## Drawings

Dimensional drawing



Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the "Downloads" tab.


# ME MAX GEH-L G 2-2 GY - Housing half shell



2202156

<https://www.phoenixcontact.com/us/products/2202156>

## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2202156>



**UL Recognized**

Approval ID: E240868

# ME MAX GEH-L G 2-2 GY - Housing half shell



2202156

<https://www.phoenixcontact.com/us/products/2202156>

## Classifications

### ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME MAX GEH-L G 2-2 GY - Housing half shell



2202156

<https://www.phoenixcontact.com/us/products/2202156>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)