

IBS SUP1 3 OPC - Slave protocol chip



2746980

<https://www.phoenixcontact.com/us/products/2746980>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Slave protocol chip, for INTERBUS

Commercial data

Item number	2746980
Packing unit	90 pc
Minimum order quantity	90 pc
Sales key	DR14
Product key	DRECAA
GTIN	4017918169459
Weight per piece (including packing)	6.674 g
Weight per piece (excluding packing)	5.882 g
Customs tariff number	85423990
Country of origin	US

IBS SUPI 3 OPC - Slave protocol chip

2746980

<https://www.phoenixcontact.com/us/products/2746980>



Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type

Protocol chip

Type

TQFP 64 (with copper block)

System properties

Module

Internal data length

4 bytes internally, external expansion is possible up to 64 bytes

Electrical properties

IC power supply voltage

5 V DC $\pm 10\%$ (DC)

Supply

Typical current consumption

40 mA (without analog control)

Interfaces

User interface

MFP interface, digital I/O (2-8 IN/OUT, 16 IN/16OUT), SPI master interface (direct serial coupling to ADC/DACs) and serial microprocessor interface

INTERBUS

Connection method

Remote bus/local bus or remote fiber optic bus

Dimensions

Width

14 mm

Height

1.2 mm

Depth

14 mm

Length

14 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection

IP00

Ambient temperature (operation)

-40 °C ... 85 °C (at max. 75 % humidity during operation)

Ambient temperature (storage/transport)

5 °C ... 30 °C (at max. 60 %)

IBS SUPI 3 OPC - Slave protocol chip

2746980

<https://www.phoenixcontact.com/us/products/2746980>



Classifications

ECLASS

ECLASS-13.0	27242605
ECLASS-15.0	27242605

ETIM

ETIM 9.0	EC001601
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

IBS SUPI 3 OPC - Slave protocol chip

2746980

<https://www.phoenixcontact.com/us/products/2746980>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com