

IB IL 24 PWR IN/2-F-PAC - Feed-in module



2862136

<https://www.phoenixcontact.com/us/products/2862136>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline power terminal, complete with accessories (connector and labeling field), 24 V DC, with fuse (main and segment voltage)

Product description

The terminal is designed for use within an Inline station. It provides a 24 V supply voltage to the main circuit (U_M) and automatically supplies power for the 24 V segment circuit (U_S). The terminal has protection against polarity reversal and surge voltage. The internal fuse protects the main and segment circuits.

Your advantages

- Supply of the 24 V main voltage U_{M}
- Feed-in or provision of the 24 V segment voltage U_S
- Diagnostic and status indicators

Commercial data

Item number	2862136
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI121
GTIN	4017918894634
Weight per piece (including packing)	84 g
Weight per piece (excluding packing)	59 g
Customs tariff number	85389099
Country of origin	DE


IB IL 24 PWR IN/2-F-PAC - Feed-in module



2862136
<https://www.phoenixcontact.com/us/products/2862136>

Technical data

Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm

Notes

Note on application	
Note on application	Only for industrial use

Interfaces

Inline local bus	
Number of interfaces	2
Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps

System properties

Module	
ID code (dec.)	none
ID code (hex)	none
Register length	0 bit
Required parameter data	0 Byte
Required configuration data	0 Byte

Product properties

Product type	I/O component
Product family	Inline
Type	modular
Installation location	Control cabinet
Number of plugs	1
Special properties	24 V DC
	U_M, U_S
	With fuse (U_M, U_S)

Insulation characteristics	
----------------------------	--

IB IL 24 PWR IN/2-F-PAC - Feed-in module



2862136

<https://www.phoenixcontact.com/us/products/2862136>

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Electrical properties

Maximum power dissipation for nominal condition	1.8 W
Test section	5 V supply, incoming remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	5 V supply, outgoing remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	7.5 V supply (bus logics)/24 V supply (I/O) 500 V AC 50 Hz 1 min
	24 V supply (I/O) / functional ground 500 V AC 50 Hz 1 min
Protective circuit	Polarity protection, surge protection
Fuse	SI 5 x 20 6, 300 AT (in scope of delivery)

Supply

Communications power U_L	7.5 V DC
I/O voltage	24 V DC
I/O voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Residual ripple	$\pm \pm 5 \%$
Max. current consumption	6 A (8 A)

Potentials: Main circuit supply (U_M)

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V ... 30 V (including all tolerances, including ripple)

Potentials: Segment circuit supply (U_S)

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Conductor connection

Connection method	Spring-cage connection
Conductor cross-section rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

IB IL 24 PWR IN/2-F-PAC - Feed-in module



2862136

<https://www.phoenixcontact.com/us/products/2862136>

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)

Mounting

Mounting type	DIN rail mounting
---------------	-------------------


IB IL 24 PWR IN/2-F-PAC - Feed-in module

2862136

<https://www.phoenixcontact.com/us/products/2862136>

Drawings

Dimensional drawing




IB IL 24 PWR IN/2-F-PAC - Feed-in module

2862136

<https://www.phoenixcontact.com/us/products/2862136>



Connection diagram




IB IL 24 PWR IN/2-F-PAC - Feed-in module

2862136

<https://www.phoenixcontact.com/us/products/2862136>



Block diagram



IB IL 24 PWR IN/2-F-PAC - Feed-in module



2862136

<https://www.phoenixcontact.com/us/products/2862136>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2862136>



DNV GL

Approval ID: TAA00000BN



LR

Approval ID: LR23398855TA



BV

Approval ID: 21725/C1 BV

BSH

Approval ID: 658a



RINA

Approval ID: ELE121121XG

ABS

Approval ID: 22-2226444-PDA



cULus Recognized

Approval ID: E140324

IB IL 24 PWR IN/2-F-PAC - Feed-in module



2862136

<https://www.phoenixcontact.com/us/products/2862136>

Classifications

ECLASS

ECLASS-13.0	27242610
ECLASS-15.0	27242610

ETIM

ETIM 9.0	EC001600
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

IB IL 24 PWR IN/2-F-PAC - Feed-in module



2862136
<https://www.phoenixcontact.com/us/products/2862136>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: n/a)
SCIP	e55f390b-cf10-46ed-b85d-e7d81be04181

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com