

PSR-SPP- 24DC/SDC4/2X1/B - Safety relays



2981499

<https://www.phoenixcontact.com/us/products/2981499>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety relay for emergency stop, safety door, and magnetic switches, as well as light grids, up to SIL 3 or Cat. 4, PL e in accordance with EN ISO 13849, 2 N/O contacts, TBUS interface, automatic or manual activation, pluggable Push-in terminal block

Your advantages

- Up to Cat. 4/PL e in accordance with ISO 13849-1, SIL 3 in accordance with EN IEC 62061, SIL 3 in accordance with IEC 61508
- Modular system with TBUS extension
- For emergency stop and safety door monitoring, plus evaluation of light grids
- 2 enabling current paths, 1 signaling current path
- 1- and 2-channel control

Commercial data

Item number	2981499
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN01
Product key	DNA211
GTIN	4046356051699
Weight per piece (including packing)	228 g
Weight per piece (excluding packing)	197.9 g
Customs tariff number	85371098
Country of origin	DE

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Safety relays
Product family	PSRclassic
Application	Emergency stop
	Safety door
	Light grid
	Magnetic switch
Control	1 and 2 channel
Mechanical service life	approx. 10^7 cycles
Relay type	Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Maximum power dissipation for nominal condition	1.68 W
Nominal operating mode	100% operating factor
Rated insulation voltage	250 V
Rated surge voltage/insulation	4 kV / Basic isolation, (safe isolation, reinforced insulation and 6 kV between input circuit and enabling current paths.)

Input data

General

Nominal input voltage U_N	24 V DC
Input voltage range in reference to U_N	0.85 ... 1.1
Typical input current at U_N	70 mA
Voltage at input/start and feedback circuit	approx. 24 V DC
Typical response time	20 ms (manual start)
	150 ms (automatic start)
Typical release time	10 ms
Recovery time	1 s
Max. permissible overall conductor resistance	50 Ω (Input and start circuits at U_S)

Output data

Contact switching type	2 enabling current paths
	1 semiconductor signaling output

PSR-SPP- 24DC/SDC4/2X1/B - Safety relays



2981499

<https://www.phoenixcontact.com/us/products/2981499>

Contact material	AgSnO ₂
Maximum switching voltage	250 V AC/DC (Enabling current paths)
	24 V (Signal output)
Minimum switching voltage	15 V AC/DC (Enabling current paths)
Limiting continuous current	6 A (Enabling current paths)
	100 mA (Signal output)
Maximum inrush current	6 A
Inrush current, minimum	25 mA (Enabling current paths)
Sq. Total current	$72 \text{ A}^2 (I_{TH}^2 = I_1^2 + I_2^2)$
Interrupting rating (ohmic load) max.	144 W (24 V DC, $\tau = 0 \text{ ms}$)
	288 W (48 V DC, $\tau = 0 \text{ ms}$)
	77 W (110 V DC, $\tau = 0 \text{ ms}$)
	88 W (220 V DC, $\tau = 0 \text{ ms}$)
	1500 VA (250 V AC, $\tau = 0 \text{ ms}$)
Maximum interrupting rating (inductive load)	48 W (24 V DC, $\tau = 40 \text{ ms}$)
	40 W (48 V DC, $\tau = 40 \text{ ms}$)
	35 W (110 V DC, $\tau = 40 \text{ ms}$)
	33 W (220 V DC, $\tau = 40 \text{ ms}$)
Switching capacity	min. 0.4 W (Enabling current paths)
Switching capacity (360/h cycles)	6 A (24 V DC)
	5 A (230 V (AC15))
Switching capacity (3600/h cycles)	3 A (24 V (DC13))
	3 A (230 V (AC15))
Output fuse	10 A gL/gG NEOZED (Enabling current paths)
	Miniature circuit breaker C6 (24 V / 20 A power supply unit)

Connection data

Connection technology

pluggable	yes
-----------	-----

Conductor connection

Connection method	Push-in connection
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 1.5 mm ² (only together with CRIMPFOX 6)
Conductor cross-section flexible, with ferrule without plastic sleeve	0.25 mm ² ... 1.5 mm ² (only together with CRIMPFOX 6)
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

Dimensions

Width	22.5 mm
Height	112 mm
Depth	114.5 mm

PSR-SPP- 24DC/SDC4/2X1/B - Safety relays



2981499

<https://www.phoenixcontact.com/us/products/2981499>

Material specifications

Color (Housing)	yellow (RAL 1018)
Housing material	PA

Characteristics

Safety data

Stop category	0
---------------	---

Safety data: EN ISO 13849

Category	4 (Undelayed contacts)
Performance level (PL)	e

Safety data: IEC 61508 - High demand

Safety Integrity Level (SIL)	3
------------------------------	---

Safety data: IEC 61508 - Low demand

Safety Integrity Level (SIL)	3
------------------------------	---

Safety data: EN IEC 62061

Safety Integrity Level (SIL)	3
------------------------------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Ambient temperature (operation)	-20 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Maximum altitude	≤ 2000 m (Above sea level)
Max. permissible humidity (storage/transport)	75 % (on average, 85% infrequently, non-condensing)
Max. permissible relative humidity (operation)	75 % (on average, 85% infrequently, non-condensing)

Mounting

Mounting type	DIN rail mounting
Mounting position	any

PSR-SPP- 24DC/SDC4/2X1/B - Safety relays




2981499

<https://www.phoenixcontact.com/us/products/2981499>


Drawings

Connection diagram



PSR-TBUS DIN rail connectors are used for cross-wiring between the modules.

Circuit diagram




Block diagram

PSR-SPP- 24DC/SDC4/2X1/B - Safety relays

2981499

<https://www.phoenixcontact.com/us/products/2981499>

Circuit diagram




2-channel emergency stop monitoring

PSR-SPP- 24DC/SDC4/2X1/B - Safety relays

2981499

<https://www.phoenixcontact.com/us/products/2981499>

Circuit diagram




Light grid monitoring

PSR-SPP- 24DC/SDC4/2X1/B - Safety relays

2981499

<https://www.phoenixcontact.com/us/products/2981499>

Circuit diagram



Two-channel magnetic switch monitoring

PSR-SPP- 24DC/SDC4/2X1/B - Safety relays



2981499

<https://www.phoenixcontact.com/us/products/2981499>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2981499>



cULus Listed

Approval ID: E140324



Functional Safety

Approval ID: 01/205/0660.04/24

PSR-SPP- 24DC/SDC4/2X1/B - Safety relays



2981499

<https://www.phoenixcontact.com/us/products/2981499>

Classifications

ECLASS

ECLASS-13.0	27371819
ECLASS-15.0	27371819
ECLASS-15.0 ASSET	27250101

ETIM

ETIM 9.0	EC001449
----------	----------

UNSPSC

UNSPSC 21.0	39122200
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: n/a)
SCIP	3ffe7659-7c07-4479-bf6c-1b797cdb1c40

EF3.0 Climate Change

CO2e kg	6.132 kg CO2e
---------	---------------