


# WST 1,5 - Warning cover

3030958

<https://www.phoenixcontact.com/us/products/3030958>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Warning cover, Strip, yellow, labeled, mounting type: plug in, for terminal block width: 4.25 mm, Number of individual labels: 5

## Your advantages

- Accidental actuation of the terminal points is prevented
- Warning labels and warning covers serve to cover and identify mains terminal blocks
- The warning labels snap into the screw and actuation shafts of the relevant terminal block
- Can be isolated lengthwise and crosswise

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3030958       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BG20          |
| Product key                          | BG2511        |
| GTIN                                 | 4017918193096 |
| Weight per piece (including packing) | 0.297 g       |
| Weight per piece (excluding packing) | 0.29 g        |
| Customs tariff number                | 49119900      |
| Country of origin                    | PL            |

# WST 1,5 - Warning cover

3030958

<https://www.phoenixcontact.com/us/products/3030958>



## Technical data

### Product properties

|                     |               |
|---------------------|---------------|
| Product type        | Klemmenmarker |
| Number of positions | 5             |
| Pitch               | 4.25 mm       |

### Marking

|                                     |         |
|-------------------------------------|---------|
| Number of individual labels         | 5       |
| Number of individual labels per row | 5       |
| Identification technology           | Plotter |

### Dimensions

|        |         |
|--------|---------|
| Width  | 3.55 mm |
| Height | 4.25 mm |
| Depth  | 4.50 mm |
| Pitch  | 4.25 mm |

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | yellow (RAL 1018)              |
| Material                               | PA                             |
| Flammability rating according to UL 94 | V2                             |
| Components                             | free from silicone and halogen |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |

#### Wipe resistance of inscriptions

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
|---------------|-------------------------------------|

#### Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

#### Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |

# WST 1,5 - Warning cover

3030958

<https://www.phoenixcontact.com/us/products/3030958>



## Ambient conditions

|                                                     |                   |
|-----------------------------------------------------|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Mounting

|               |         |
|---------------|---------|
| Mounting type | plug in |
|---------------|---------|

# WST 1,5 - Warning cover

3030958

<https://www.phoenixcontact.com/us/products/3030958>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-15.0 | 27281107 |
| ECLASS-13.0 | 27281107 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001777 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 55121700 |
|-------------|----------|

# WST 1,5 - Warning cover



3030958  
<https://www.phoenixcontact.com/us/products/3030958>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |
| EF3.0 Climate Change                    |                            |
| CO2e kg                                 | 0.008 kg CO2e              |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)