

CARRIER/L-EMP (1000X15) TR - Marker carriers



0829560

<https://www.phoenixcontact.com/us/products/0829560>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Profile, self-adhesive, 1000 mm long, for accommodating UC-,/US-, LS-, and EMT (EX15)R material, 15 mm height

Commercial data

Item number	0829560
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BG12
Product key	BG241A
GTIN	4046356614917
Weight per piece (including packing)	27.5 g
Weight per piece (excluding packing)	27.5 g
Customs tariff number	39162000
Country of origin	DE

CARRIER/L-EMP (1000X15) TR - Marker carriers



0829560

<https://www.phoenixcontact.com/us/products/0829560>

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	1000 mm
Height	17.6 mm
Depth	6.6 mm

Material specifications

RoHS compliant	yes
Adhesive	Acrylic
Color	transparent
Material	PVC
Components	Silicone-free

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.
Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	96 h
Maximum temperature	+60 °C

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
---------------------------------	------------------

CARRIER/L-EMP (1000X15) TR - Marker carriers



0829560

<https://www.phoenixcontact.com/us/products/0829560>

Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Mounting

Mounting type	adhesive
---------------	----------

CARRIER/L-EMP (1000X15) TR - Marker carriers



0829560

<https://www.phoenixcontact.com/us/products/0829560>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 9.0	EC002248
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CARRIER/L-EMP (1000X15) TR - Marker carriers



0829560
<https://www.phoenixcontact.com/us/products/0829560>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.495 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com