

# WML 14 (25X19)A4 CUS - Cable marker



0830705

<https://www.phoenixcontact.com/us/products/0830705>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker, Sheet, can be ordered: in sheets, white, labeled according to customer specifications, cable diameter range: 6.1 ... 14.2 mm, mounting type: adhesive, cable diameter:  $\leq$  14.2 mm, Number of individual labels: 28, text field height: 19 mm, text field width: 25 mm



## Your advantages

- For indoor applications: high resistance to dirt and abrasion due to the protective laminate
- Firmly defined positioning of labels thanks to the adhesive system
- Broad diameter range with many different applications inside and outside the control cabinet
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- The wrap-around labels do not create any additional volume, so the cable can also be pulled through cable ducts, for example
- For cylindrical objects, single wires, and cables

## Commercial data

Item number	0830705
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8134
GTIN	4046356718899
Weight per piece (including packing)	15.35 g
Weight per piece (excluding packing)	15.35 g
Country of origin	PL

# WML 14 (25X19)A4 CUS - Cable marker



0830705

<https://www.phoenixcontact.com/us/products/0830705>

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Number of individual labels	28
Number of individual labels per row	7
Identification technology	Office laser printing

### Dimensions

Width	25 mm
Length	63.5 mm

### Material specifications

RoHS compliant	yes
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester
Components	Free from halogen and cadmium

### Cable/line

External cable diameter	≤ 14.20 mm
	6.1 mm ... 14.2 mm

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (storage/transport)	23 °C
Permissible humidity (storage/transport)	50 %
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	2 years

### Standards and regulations

# WML 14 (25X19)A4 CUS - Cable marker



0830705

<https://www.phoenixcontact.com/us/products/0830705>

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	adhesive
---------------	----------

# WML 14 (25X19)A4 CUS - Cable marker



0830705

<https://www.phoenixcontact.com/us/products/0830705>

## Classifications

### ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

### ETIM

ETIM 9.0	EC001530
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# WML 14 (25X19)A4 CUS - Cable marker



0830705  
<https://www.phoenixcontact.com/us/products/0830705>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)