

WML 36 (25X38)A4 YE CUS - Cable marker



0830710

<https://www.phoenixcontact.com/us/products/0830710>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker, Sheet, can be ordered: in sheets, yellow, labeled according to customer specifications, cable diameter range: 12.1 ... 36.4 mm, mounting type: adhesive, cable diameter: ≤ 36.4 mm, Number of individual labels: 14, text field height: 38 mm, text field width: 25 mm



Your advantages

- For indoor applications: high resistance to dirt and abrasion due to the protective laminate
- Firmly defined positioning of labels thanks to the adhesive system
- Broad diameter range with many different applications inside and outside the control cabinet
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- The wrap-around labels do not create any additional volume, so the cable can also be pulled through cable ducts, for example
- For cylindrical objects, single wires, and cables

Commercial data

Item number	0830710
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8134
GTIN	4046356718943
Weight per piece (including packing)	17 g
Weight per piece (excluding packing)	17 g
Country of origin	PL

WML 36 (25X38)A4 YE CUS - Cable marker



0830710

<https://www.phoenixcontact.com/us/products/0830710>

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	14
Number of individual labels per row	7
Identification technology	Office laser printing

Dimensions

Width	25 mm
Length	140 mm

Material specifications

RoHS compliant	yes
Adhesive	Acrylic
Color	yellow (RAL 1018)
Material	Polyester
Components	Free from halogen and cadmium

Cable/line

External cable diameter	≤ 36.40 mm
	12.1 mm ... 36.4 mm

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (storage/transport)	23 °C
Permissible humidity (storage/transport)	50 %
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	2 years

Standards and regulations

WML 36 (25X38)A4 YE CUS - Cable marker



0830710

<https://www.phoenixcontact.com/us/products/0830710>

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

WML 36 (25X38)A4 YE CUS - Cable marker



0830710

<https://www.phoenixcontact.com/us/products/0830710>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

WML 36 (25X38)A4 YE CUS - Cable marker



0830710

<https://www.phoenixcontact.com/us/products/0830710>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com