

PABA WH/10 - Insert label

1013753

<https://www.phoenixcontact.com/us/products/1013753>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insert label, Strip, white, unmarked, can be labeled with: CMS-P1-PLOTTER, cable diameter range: 0.6 ... 7 mm, mounting type: slide-on, Number of individual labels: 20, text field height: 4 mm, text field width: 10 mm

Commercial data

Item number	1013753
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG20
Product key	BG2213
GTIN	4017918013943
Weight per piece (including packing)	5.754 g
Weight per piece (excluding packing)	3.84 g
Customs tariff number	39269097
Country of origin	CN

Technical data

Notes

General	Can be labeled with CMS
---------	-------------------------

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	20
Number of individual labels per row	1

Dimensions

Width	9.9 mm
Height	3.96 mm
Depth	1.8 mm

Material specifications

Color	white (RAL 9010)
Flammability rating according to UL 94	V0
Base element material	ABS

Cable/line

External cable diameter	0.6 mm ... 7 mm
-------------------------	-----------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h

PABA WH/10 - Insert label



1013753

<https://www.phoenixcontact.com/us/products/1013753>

Rating 80 °C (105 °C)	Test passed
-----------------------	-------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-15 °C ... 65 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Mounting

Mounting type	slide-on
---------------	----------

PABA WH/10 - Insert label

1013753

<https://www.phoenixcontact.com/us/products/1013753>



Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

PABA WH/10 - Insert label

1013753
<https://www.phoenixcontact.com/us/products/1013753>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.032 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com