

SACC-E-M 8MS-6CON-M 8/0,5 - Device connector front mounting



1542664

<https://www.phoenixcontact.com/us/products/1542664>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, 6-position, Pin, straight, M8, A-coding, Individual wires, cable length: 0.5 m, 0.14 mm², PVC litz wire

Your advantages

- Preassembled with litz wires for immediate use
- Customer-specific assemblies and litz wire lengths available
- Sealed on the litz wire side for optimum leak-tightness
- Standard pin assignments and codings for signal transmission with a uniform design-in design

Commercial data

Item number	1542664
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB22
Product key	ABQIAA
GTIN	4046356097697
Weight per piece (including packing)	13.5 g
Weight per piece (excluding packing)	13 g
Customs tariff number	85444290
Country of origin	DE

SACC-E-M 8MS-6CON-M 8/0,5 - Device connector front mounting



1542664

<https://www.phoenixcontact.com/us/products/1542664>

Technical data

Mounting

Mounting type	Front mounting (M8 x 0,5)
Tightening torque	0.8 Nm ... 1 Nm (Installation-side)

Product properties

Product type	Circular connectors (device side)
Application	Data
Number of positions	6
No. of cable outlets	1
Shielded	no
Coding	A
Thread type	M8

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	Viton
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Brass, nickel-plated
Conductor material	Tin-plated Cu litz wires

Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V AC
	30 V DC
Nominal current I_N	1.5 A
Max. conductor resistance	80 Ω/km

Connection data

Conductor connection

Connection method	Individual wires
Contact connection type	Pin
Conductor cross-section	0.14 mm ²

SACC-E-M 8MS-6CON-M 8/0,5 - Device connector front mounting



1542664

<https://www.phoenixcontact.com/us/products/1542664>

Tightening torque	0.8 Nm ... 1 Nm (Installation-side)
-------------------	-------------------------------------

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M8
Coding	A

Cable/line

Cable length	0.5 m
Cable type	PVC litz wire
Wire diameter incl. insulation	1.3 mm $\pm$ 0.1 mm
Single wire, color	black, brown, blue, white, gray, pink
Cable cross section	0.14 mm ²
Conductor material	Tin-plated Cu litz wires
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Material wire insulation	PVC / UL
Thickness, insulation	0.38 mm
Nominal voltage, cable	300 V
Test voltage, cable	2000 V AC
Cable resistance	$\geq 80 \Omega/\text{km}$
Cable insulation resistance	$\geq 20 \text{ M}\Omega \cdot \text{km}$
Ambient temperature (operation)	-40 °C ... 85 °C (cable, fixed installation) -10 °C ... 105 °C

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C
Ambient temperature (operation) (fixed installation)	-40 °C ... 105 °C (without mechanical actuation)
Ambient temperature (operation) (Cable, flexible installation)	-10 °C ... 105 °C
Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 85 °C (cable, fixed installation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

SACC-E-M 8MS-6CON-M 8/0,5 - Device connector front mounting




1542664

<https://www.phoenixcontact.com/us/products/1542664>

Drawings

Schematic diagram



Pin assignment M8 plug, 6-pos., view male side

SACC-E-M 8MS-6CON-M 8/0,5 - Device connector front mounting



1542664

<https://www.phoenixcontact.com/us/products/1542664>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1542664>

 cUL Recognized Approval ID: E221474-20070307				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	1.5 A	26	-

 UL Recognized Approval ID: E221474-20070307				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	1.5 A	26	-

SACC-E-M 8MS-6CON-M 8/0,5 - Device connector front mounting



1542664

<https://www.phoenixcontact.com/us/products/1542664>

Classifications

ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

ETIM

ETIM 9.0	EC003570
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-E-M 8MS-6CON-M 8/0,5 - Device connector front mounting



1542664

<https://www.phoenixcontact.com/us/products/1542664>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	98e417ab-ee9f-46e8-9cc1-1b658135af55

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com