

IPD WD 3P2,5 0,5 M20 GY - Panel feed-through



1047347

<https://www.phoenixcontact.com/us/products/1047347>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel feed-through, Direct connection, connection method: Single wires/ Push-in connection, number of positions: 2+PE, M20, 0.5 mm² ... 2.5 mm², 450 V, 16 A, PA, light gray, external cable diameter: 6 mm ... 9 mm and 8 mm ... 13 mm, 2.5 mm², cable length: 0.5 m

Your advantages

- Convenient: quick and easy assembly without special tools
- Fast and easy startup, thanks to tool-free Push-in connection technology
- Reliable installation in harsh environments with IP66, IP68, and IP69K throughout the entire system

Commercial data

Item number	1047347
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF51
Product key	AF6IAB
GTIN	4055626647838
Weight per piece (including packing)	102.1 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85366990
Country of origin	CN

IPD WD 3P2,5 0,5 M20 GY - Panel feed-through



1047347

<https://www.phoenixcontact.com/us/products/1047347>

Technical data

Product properties

Product type	Panel feed-through
Product family	IPD
Number of positions	3
Connection profile	2+PE
Position marking	L, N, PE

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data


Connection technology

Connection method On the device side	Single wires
Connection method On the field side	Push-in connection
Frequency of connections between conductors of the same cross section	max. 10

Conductor connection

Conductor cross section flexibel	0.5 mm ² ... 2.5 mm ²
Conductor cross section solid	0.5 mm ² ... 2.5 mm ²
Conductor cross section with ferrule	0.5 mm ² ... 2.5 mm ²
Connection cross section AWG	20 ... 14

Dimensions

Dimensional drawing	
Width	28.6 mm
Length	85.7 mm

Electrical properties

Rated surge voltage (III/3)	6 kV
Rated current	16 A
Rated voltage (III/3)	450 V
Nominal voltage U _N	450 V AC 450 V DC
Nominal current I _N	16 A (observe derating)

Mechanical properties

IPD WD 3P2,5 0,5 M20 GY - Panel feed-through



1047347

<https://www.phoenixcontact.com/us/products/1047347>

Mechanical data

Insertion/withdrawal cycles	10
-----------------------------	----

Material specifications

Color (Housing)	light gray (RAL 7035)
Material Housing	PA
Material Seal	NBR (Field)
	EPDM (Device)
Flammability rating according to UL 94	V0
Contact material	Cu
Contact surface material	Ni/Sn

Cable/line

Cable length	0.5 m
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 class 5
External cable diameter	6 mm ... 9 mm
	8 mm ... 13 mm
Stripping length of the individual wire	10 mm
Position marking	L, N, PE
Single wire, color	brown, blue, green/yellow
Cable cross section	2.5 mm²
Material wire insulation	PVC
Halogen-free	no

Mounting

Mounting type	Front mounting M20
---------------	--------------------


Environmental and real-life conditions

Ambient conditions


Degree of protection	IP66
	IP68 (2 m / 24 h)
	IP69K
Impact strength	IK07
Ambient temperature (operation)	-40 °C ... 90 °C (T = 45 °C)
Temperature when conductor connected	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 90 °C
Resistance to UV radiation	yes

Drawings


Dimensional drawing




Diagram



Derating diagram for 1.0 mm²



Derating diagram for 1.5 mm²



Derating diagram for 2.5 mm²

IPD WD 3P2,5 0,5 M20 GY - Panel feed-through



1047347

<https://www.phoenixcontact.com/us/products/1047347>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1047347>

 VDE Zeichengenehmigung Approval ID: 40049992				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	450 V	20 A	-	0.5 - 2.5

 UL Listed Approval ID: E468743				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
Only rigid conductors	600 V	15 A	- 14	- 14
multi-stranded with ferrule	600 V	15 A	- 14	- 14

 cUL Listed Approval ID: E468743				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	20 A	- 14	-

DNV Approval ID: TAE00004G2				
---------------------------------------	--	--	--	--

IPD WD 3P2,5 0,5 M20 GY - Panel feed-through



1047347

<https://www.phoenixcontact.com/us/products/1047347>

Classifications

ECLASS

ECLASS-13.0	27440602
ECLASS-15.0	27440602

ETIM

ETIM 9.0	EC002566
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

IPD WD 3P2,5 0,5 M20 GY - Panel feed-through



1047347
<https://www.phoenixcontact.com/us/products/1047347>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com