

# RC-09P1N8A8049 - Cable connector



1595404

<https://www.phoenixcontact.com/us/products/1595404>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, straight, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 6.5 mm ... 7.5 mm, coding: N, this item is expected to be lead-free from Q1 2027 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1595404
Packing unit	20 pc
Minimum order quantity	1 pc
Product key	ABRAFA
GTIN	4046356206525
Weight per piece (including packing)	71.435 g
Weight per piece (excluding packing)	67.628 g
Country of origin	DE

# RC-09P1N8A8049 - Cable connector



1595404

<https://www.phoenixcontact.com/us/products/1595404>

## Technical data

### Notes

Order information:	Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately
--------------------	--

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Note	Order information: Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number Contact (Contact group 1)	1
Diameter Contact (Contact group 1)	2 mm
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number Contact (Contact group 2)	8
Diameter Contact (Contact group 2)	1 mm
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

#### Housing

Note	Order contact inserts separately
Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	Metal
Degree of protection (plugged in)	IP65 IP67

# RC-09P1N8A8049 - Cable connector



1595404

<https://www.phoenixcontact.com/us/products/1595404>

	IP68
Seal	
External cable diameter	6.5 mm ... 7.5 mm

## Environmental and real-life conditions

Ambient conditions	
Permissible humidity (storage/transport)	50 % ... 65 %

# RC-09P1N8A8049 - Cable connector


1595404

<https://www.phoenixcontact.com/us/products/1595404>



## Drawings

Schematic diagram



Connector pin assignment


# RC-09P1N8A8049 - Cable connector

1595404

<https://www.phoenixcontact.com/us/products/1595404>



Schematic diagram




Connector pin assignment

# RC-09P1N8A8049 - Cable connector

1595404

<https://www.phoenixcontact.com/us/products/1595404>

Schematic diagram



Connector pin assignment

# RC-09P1N8A8049 - Cable connector



1595404

<https://www.phoenixcontact.com/us/products/1595404>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-09P1N8A8049 - Cable connector



1595404

<https://www.phoenixcontact.com/us/products/1595404>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	3ef53607-1363-4379-9970-cc23c62d01b9

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)