

# UBAL 50 BN - High-current terminal block



1086470

<https://www.phoenixcontact.com/us/products/1086470>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



High-current terminal block, nom. voltage: 1000 V, nominal current: 145 A, number of connections: 2, number of positions: 1, connection method: Screw connection, Rated cross section: 50 mm<sup>2</sup>, cross section: 6 mm<sup>2</sup> - 50 mm<sup>2</sup>, Rated cross section: 50 mm<sup>2</sup>, cross section: 4 mm<sup>2</sup> - 50 mm<sup>2</sup>, mounting type: NS 35/15, NS 35/7,5, color: brown

## Your advantages

- Maintenance-free terminal points that are greased beforehand simplify the connection of aluminum conductors
- Tailor-made screw connection for multi-stranded aluminum conductors and copper wires
- Extremely robust housing made from fiberglass-reinforced polyamide with V0 approval
- The special design of the UBAL enables the simultaneous connection of aluminum and copper conductors in various connections

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1086470       |
| Packing unit                         | 20 pc         |
| Minimum order quantity               | 20 pc         |
| Sales key                            | BE13          |
| Product key                          | BE1311        |
| GTIN                                 | 4055626877969 |
| Weight per piece (including packing) | 48.92 g       |
| Weight per piece (excluding packing) | 22.22 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | EE            |

# UBAL 50 BN - High-current terminal block



1086470

<https://www.phoenixcontact.com/us/products/1086470>

## Technical data

### Notes

|         |                                                            |
|---------|------------------------------------------------------------|
| General | Terminal block for aluminum and copper conductors (AL-CU)  |
| General |                                                            |
| Note    | We recommend using ferrules when using flexible conductor. |

### Product properties

|                       |                             |
|-----------------------|-----------------------------|
| Product type          | Feed-through terminal block |
| Product family        | UBAL                        |
| Number of positions   | 1                           |
| Number of connections | 2                           |
| Number of rows        | 1                           |
| Potentials            | 1                           |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                                                 |        |
|-------------------------------------------------|--------|
| Rated surge voltage                             | 8 kV   |
| Maximum power dissipation for nominal condition | 4.73 W |

### Connection data

|                       |                    |
|-----------------------|--------------------|
| Nominal cross section | 50 mm <sup>2</sup> |
|-----------------------|--------------------|

### Aluminum conductor

|                                  |                                                                                                                                                                                                      |
|----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Connection method                | Screw connection                                                                                                                                                                                     |
| Screw thread                     | M10                                                                                                                                                                                                  |
| Note                             | Screws with hexagonal socket                                                                                                                                                                         |
|                                  | The following values apply to aluminum conductors                                                                                                                                                    |
|                                  | The values for aluminum conductors relate to rigid and multi-stranded conductors in accordance with EN 60228. Application notes on connecting aluminum conductors can be found in the download area. |
| Tightening torque                | 12 Nm                                                                                                                                                                                                |
| Stripping length                 | 23 mm                                                                                                                                                                                                |
| Connection in acc. with standard | IEC 61238-1                                                                                                                                                                                          |
| Conductor cross-section rigid    | 6 mm <sup>2</sup> ... 50 mm <sup>2</sup>                                                                                                                                                             |
| Cross section AWG                | 6 ... 1/0 (converted acc. to IEC)                                                                                                                                                                    |
| Nominal current                  | 145 A                                                                                                                                                                                                |
| Maximum load current             | 145 A (with 50 mm <sup>2</sup> conductor cross-section – test current in accordance with IEC 61238-1)                                                                                                |
| Nominal voltage                  | 1000 V                                                                                                                                                                                               |
| Nominal cross section            | 50 mm <sup>2</sup>                                                                                                                                                                                   |

# UBAL 50 BN - High-current terminal block



1086470

<https://www.phoenixcontact.com/us/products/1086470>

## Copper conductor

|                                                                   |                                                                                                          |
|-------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------|
| Note                                                              | The following values apply to copper wires<br>Flexible conductors, class 5, in accordance with EN 60228. |
| Tightening torque                                                 | 4 ... 12 Nm                                                                                              |
| Stripping length                                                  | 23 mm                                                                                                    |
| Connection in acc. with standard                                  | IEC 60947-7-1                                                                                            |
| Conductor cross-section rigid                                     | 4 mm <sup>2</sup> ... 50 mm <sup>2</sup>                                                                 |
| Cross section AWG                                                 | 6 ... 1/0 (converted acc. to IEC)                                                                        |
| Conductor cross-section flexible                                  | 2.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>                                                               |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 2.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>                                                               |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 2.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>                                                               |
| 2 conductors with same cross section, flexible                    | 2.5 mm <sup>2</sup> ... 16 mm <sup>2</sup>                                                               |
| Nominal current                                                   | 150 A                                                                                                    |
| Maximum load current                                              | 150 A (with 50 mm <sup>2</sup> conductor cross-section)                                                  |
| Nominal voltage                                                   | 1000 V                                                                                                   |
| Nominal cross section                                             | 50 mm <sup>2</sup>                                                                                       |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 19.2 mm |
| Height             | 82.5 mm |
| Depth              | 51 mm   |
| Depth on NS 35/7,5 | 51 mm   |
| Depth on NS 35/15  | 58.5 mm |
| Hole diameter      | 2.75 mm |

## Material specifications

|                                                                  |                  |
|------------------------------------------------------------------|------------------|
| Color                                                            | brown (RAL 8028) |
| Flammability rating according to UL 94                           | V0               |
| Insulating material group                                        | II               |
| Insulating material                                              | PA               |
| Relative insulation material temperature index (Elec., UL 746 B) | 400 °C           |

## Electrical tests

### Surge voltage test

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 8 kV        |
| Result                | Test passed |

### Temperature-rise test

|                                                 |                                |
|-------------------------------------------------|--------------------------------|
| Requirement temperature-rise test               | Increase in temperature ≤ 45 K |
| Result                                          | Test passed                    |
| Short-time withstand current 50 mm <sup>2</sup> | 6 kA                           |
| Result                                          | Test passed                    |

### Power-frequency withstand voltage

# UBAL 50 BN - High-current terminal block



1086470

<https://www.phoenixcontact.com/us/products/1086470>

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 2.2 kV      |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

### Attachment on the carrier

|                         |             |
|-------------------------|-------------|
| DIN rail/fixing support | NS 35       |
| Test force setpoint     | 10 N        |
| Result                  | Test passed |

### Test for conductor damage and slackening

|                                |                                                             |
|--------------------------------|-------------------------------------------------------------|
| Rotation speed                 | 10 rpm                                                      |
| Revolutions                    | 135                                                         |
| Conductor cross-section/weight | 2.5 mm <sup>2</sup> / 0.7 kg<br>50 mm <sup>2</sup> / 9.5 kg |
| Result                         | Test passed                                                 |

## Environmental and real-life conditions

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 10 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|                        |                                                  |
|------------------------|--------------------------------------------------|
| Specification          | DIN EN 50155 (VDE 0115-200):2018-05              |
| Spectrum               | Long life test category 2, bogie-mounted         |
| Frequency              | f <sub>1</sub> = 5 Hz to f <sub>2</sub> = 250 Hz |
| ASD level              | 6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz        |
| Acceleration           | 3.12g                                            |
| Test duration per axis | 5 h                                              |
| Test directions        | X-, Y- and Z-axis                                |
| Result                 | Test passed                                      |

### Shocks

|                                |                                   |
|--------------------------------|-----------------------------------|
| Pulse shape                    | Half-sine                         |
| Acceleration                   | 30g                               |
| Shock duration                 | 18 ms                             |
| Number of shocks per direction | 3                                 |
| Test directions                | X-, Y- and Z-axis (pos. and neg.) |
| Result                         | Test passed                       |

# UBAL 50 BN - High-current terminal block



1086470

<https://www.phoenixcontact.com/us/products/1086470>

## Ambient conditions

|                                          |                                                                                                                              |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)                                                    |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                                                                              |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                                                                              |
| Permissible humidity (operation)         | 20 % ... 90 %                                                                                                                |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                                                                                |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 61238-1   |
|                                  | IEC 60947-7-1 |

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/15  |
|               | NS 35/7,5 |

# UBAL 50 BN - High-current terminal block

1086470

<https://www.phoenixcontact.com/us/products/1086470>



## Drawings

### Circuit diagram



# UBAL 50 BN - High-current terminal block



1086470

<https://www.phoenixcontact.com/us/products/1086470>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1086470>



**EAC**

Approval ID: KZ7500651131219505

# UBAL 50 BN - High-current terminal block



1086470  
<https://www.phoenixcontact.com/us/products/1086470>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
| ECLASS-15.0 | 27250101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|



# UBAL 50 BN - High-current terminal block



1086470  
<https://www.phoenixcontact.com/us/products/1086470>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)