

ZAP 25 - Crimping tool, pneumatic



1203110

<https://www.phoenixcontact.com/us/products/1203110>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pneumatic crimping pliers, for ferrules in accordance with DIN 46228-1: 1992-08 and DIN 46228-4: 1990-09, for conductor cross-section 0.25 - 2.5 mm²

Your advantages

- These crimping pliers are pneumatic tools for ferrules with a cross section range of 0.25 mm² ... 2.5 mm²
- The ZAP 25 has a Duo-Press die, allowing both front and lateral conductor entry

Commercial data

Item number	1203110
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH3232
GTIN	4017918018085
Weight per piece (including packing)	761.9 g
Weight per piece (excluding packing)	761.9 g
Customs tariff number	84671900
Country of origin	DE

ZAP 25 - Crimping tool, pneumatic



1203110

<https://www.phoenixcontact.com/us/products/1203110>

Technical data

Product properties

Product type	Automatic crimping device
Compression	trapezoidal
Air consumption per compression	0.2 l
Pressure range	4.00 bar ... 6.00 bar
Product property	Start the crimping cycle using the manual switch
	Duo press die for front and lateral conductor entry
	Eye for using a balancer
	1 die nest
	Die width: 12 mm
	Insertion funnel allows for easy positioning
Crimping width	12.00 mm

Electrical properties

Frequency range	0 Hz
-----------------	------

Connection data

Conductor connection

Cross section range, metric	0.25 mm ² ... 2.5 mm ² (2 x 0.5 mm ² ... 2 x 1.5 mm ²)
-----------------------------	---

Dimensions

Width	44 mm
Height	44 mm
Length	200 mm


ZAP 25 - Crimping tool, pneumatic




1203110


<https://www.phoenixcontact.com/us/products/1203110>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1203110>



EAC
Approval ID: RU C-DE.AI30.B.01549



EAC
Approval ID: 0278662

ZAP 25 - Crimping tool, pneumatic



1203110

<https://www.phoenixcontact.com/us/products/1203110>

Classifications

ECLASS

ECLASS-13.0	17130101
ECLASS-15.0	17130101

ETIM

ETIM 9.0	EC002778
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

ZAP 25 - Crimping tool, pneumatic



1203110
<https://www.phoenixcontact.com/us/products/1203110>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com