

CF 3000-2,5 120V - Automatic stripping and crimping device



1205516

<https://www.phoenixcontact.com/us/products/1205516>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Automatic stripping and crimping device, 120 V version, for taped insulated ferrules 0.25 mm² ... 2.5 mm², sleeve length 8 mm, incl. 0.5 mm² ... 2.5 mm² conversion kits

Your advantages

- Particularly suitable for pre-assembling conductors
- Suitable for class 2 and class 5 PVC conductors (H05V-K/H07V-K).
Conductors with special insulating material and stranding can only be processed to a limited degree and with reservations.
- The conductor is stripped in a single step and crimped with a ferrule to a high standard of quality
- The compact automatic stripping and crimping device can be used to process taped ferrules with insulating collars according to DIN 46228-4
- Color coding according to ferrule standard DIN 46228-4 makes the assignment of modification components really clear
- The automatic device can be adapted to various cross sections in under a minute
- Thanks to its compact and lightweight design, it can also be used as a portable solution for transport between different work locations
- Up to 1200 conductors can be processed an hour

Commercial data

Item number	1205516
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH3231
GTIN	4017918129125
Weight per piece (including packing)	15,710 g
Weight per piece (excluding packing)	15,710 g
Customs tariff number	84798100
Country of origin	DE

CF 3000-2,5 120V - Automatic stripping and crimping device



1205516

<https://www.phoenixcontact.com/us/products/1205516>

Technical data

Notes

General	Suitable for class 2 and 5 standard PVC conductors (H05V-K/H07V-K). Other conductor and insulation types can be processed to a limited extent.
---------	--

Product properties

Product type	Automatic crimping device
Compression	trapezoidal
Conductor type	PVC
Insertion length minimum	49 mm
Product property	Tool-free conversion
	Color-coded conversion kits
	Integrated counter that can be reset
	Processing of taped ferrules
	Including case with conversion kits 0.5 mm ² ... 2.5 mm ²
	Suitable for class 2 and class 5 standard PVC conductors (H05V-K/H07V-K). Other conductor and insulation types can be processed to a limited extent
	Carrying handle for changing workstations
Min. cross section	0.25 mm ²
Max. cross section	2.5 mm ²
AWG min	24
AWG max	14

Electrical properties

Frequency range	60 Hz
Power consumption	80 W

Supply

Supply voltage	120 V AC
Supply voltage range	120 V AC (60 Hz)

Connection data

Conductor connection

Cross section range, metric	0.25 mm ² ... 2.5 mm ²
Cross section range AWG	24 ... 14
Stripping length	11.5 mm

Dimensions

Width	165 mm
Height	300 mm
Length	320 mm

1205516
<https://www.phoenixcontact.com/us/products/1205516>

Connector

Type of plug	Pin connector pattern type B
--------------	------------------------------

Standards and regulations

Tests	DIN 46228-4: 1990-09
-------	----------------------

CF 3000-2,5 120V - Automatic stripping and crimping device



1205516

<https://www.phoenixcontact.com/us/products/1205516>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1205516>



EAC

Approval ID: RU C-DE.AI30.B.01549

CF 3000-2,5 120V - Automatic stripping and crimping device



1205516

<https://www.phoenixcontact.com/us/products/1205516>

Classifications

ECLASS

ECLASS-13.0	17130101
ECLASS-15.0	17130101

ETIM

ETIM 9.0	EC002778
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CF 3000-2,5 120V - Automatic stripping and crimping device



1205516

<https://www.phoenixcontact.com/us/products/1205516>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a10e10e3-ac34-4210-af4c-de15ee21e8b3

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com