

EV-HPC-PCU-01 - Cooling unit



1237881

<https://www.phoenixcontact.com/us/products/1237881>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect, CCS type 1, CCS type 2, Cooling unit, Accessories, length: 1.5 m, with variable-speed fan, with variable-speed pump, for cooling the cooling liquid of a Phoenix Contact HPC DC charging cable

Commercial data

Item number	1237881
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	EM01
Product key	XWBLNY
GTIN	4063151344757
Weight per piece (including packing)	17,440 g
Weight per piece (excluding packing)	16,299 g
Customs tariff number	84195080
Country of origin	DE

EV-HPC-PCU-01 - Cooling unit



1237881

<https://www.phoenixcontact.com/us/products/1237881>

Technical data

Product properties

Product type	Cooling unit
Product family	CHARX connect
Technology	High Power Charging Combined Charging System
Application	for cooling the cooling liquid of a Phoenix Contact HPC DC charging cable for installation in e-mobility charging stations (EVSE)
Design	with variable-speed fan with variable-speed pump
Manufacturer	HYDAC Cooling GmbH
Charging standard	CCS type 1 CCS type 2
Charging mode	Mode 4

Electrical properties

Cooling system

Cooling	Liquid-air cooling system (passive) semi-closed cooling circuit
Coolant	50% water, 50% glycol (Glysofor N)
Volume range	≤ 60 db(A) (with free-standing system and 1 m distance)
Supply voltage	24 V DC (Fan) 24 V DC (Pump)
Control voltage range	0.00 V DC ... 10.00 V DC (Fan) 0.00 V DC ... 10.00 V DC (Pump)
Current consumption	max. 1.97 A (Fan) max. 1.8 A (Pump)

Interfaces

Function interface: Cooling system

Interface description	Quick release couplings, inflow and return flow, for hoses with an outer diameter of 12 mm
-----------------------	--------------------------------------------------------------------------------------------

Function interface: Fan

Cable structure	4 x 0.5 mm ²
Single-core wire	Power supply RD Reference ground BU Speed output WH Control input YE

Function interface: Pump

Cable structure	2 x 0.34 mm ² + 5 x 0.14 mm ²
-----------------	-----------------------------------------------------

EV-HPC-PCU-01 - Cooling unit



1237881

<https://www.phoenixcontact.com/us/products/1237881>

Single-core wire	Power supply RD
	Reference ground BK
	Motor shutoff signal GN
	Speed output BN
	Control input YE
	RS-485 Modbus WH can only be used by the manufacturer
	RS-485 Modbus BU can only be used by the manufacturer

Function interface: Level sensor

connection	Plug straight M12 A
------------	---------------------

Material specifications

Material (Housing)	Aluminum
	Stainless steel

Cable/line

Cable length	1.5 m (Fan)
	1.5 m (Pump)
Cable length	1.5 m (Fan)
Cable length	1.5 m (Pump)

Mechanical properties

Cooling capacity	approx. 0.06 kW/K (at 2 l/min)
Volumetric flow	approx. 2 l/min (at 1 bar)
Coolant	50% water, 50% glycol (Glysofor N)

Environmental and real-life conditions

Ambient conditions

Degree of protection (Fans)	IP55 (Fan)
Degree of protection (Pump)	IP65 (Pump)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 50 °C
Altitude	max. 1000 m (above sea level)
Volume range	≤ 60 db(A) (with free-standing system and 1 m distance)

EV-HPC-PCU-01 - Cooling unit


1237881

<https://www.phoenixcontact.com/us/products/1237881>



Drawings

Schematic diagram



Coolant tank fill-level sensor connected via M12 male with A-coding

EV-HPC-PCU-01 - Cooling unit



1237881

<https://www.phoenixcontact.com/us/products/1237881>

Classifications

ECLASS

ECLASS-13.0	27144792
ECLASS-15.0	27144792

ETIM

ETIM 9.0	EC002884
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

EV-HPC-PCU-01 - Cooling unit



1237881

<https://www.phoenixcontact.com/us/products/1237881>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead titanium zirconium oxide(CAS: 12626-81-2)
	Lead(CAS: 7439-92-1)
SCIP	052e4ff5-7318-4019-8f73-22974279b3e6

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com