

THERMOMARK E.WIRE SET US - Applicator set



1287046

<https://www.phoenixcontact.com/us/products/1287046>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Equipment set consisting of the THERMOMARK E.WIRE applicator and the compatible THERMOMARK E.300 printing system for printing and applying movable E-WM... markers on wires and cables.

Product description

When it comes to wire and cable marking, the THERMOMARK E.WIRE set elevates productivity to the next level. The combination of the THERMOMARK E.300 roll printer and the THERMOMARK E.WIRE applicator offers maximum efficiency for wire and cable identification processes. This provides you with an automated printing and application system that enables you to achieve time savings of up to 70% compared to manual identification processes.

The movable markers are suitable for all types of cylindrical objects as well as twisted wires. Thanks to their triangular shape, they can be marked on all three sides. In this process, the THERMOMARK E.WIRE automatically measures the diameter of the cylindrical object, cuts the E-WM... marking foil in continuous format printed by the THERMOMARK E.300 BASIC to the appropriate length, places this around the cylindrical object, and then seals the marker shut with a heat-sealed joint. This results in a captive marker that is optimally tailored to the diameter and can also move radially and axially. Thanks to this unique system, all diameters between 1.8 mm/0.07" and 5.6 mm/0.22" can be marked efficiently using just one type of material.

Scope of supply:

THERMOMARK E.WIRE (1203216), TM E.WIRE/E.SLEEVE-PR pressure roller (1259203), THERMOMARK E.300 BASIC, power cable (pin connector pattern: type F), USB cable, and multilingual packing slip.

Note:

The THERMOMARK E.300 (D) BASIC printing system is equipped for immediate use in combination with the corresponding applicator. It differs from the THERMOMARK E.300 (D)/E.600 (D) standard printer in that it has a reduced scope of supply. The TM E.300/E.600-FRONT COVER front cover (1285305), TM E.300/E.600-TEAR OFF PLATE tear-off plate (1263118), TRM-PRESSURE ROLLER STANDARD standard pressure roller (0804655), EML (20X8)R/TL label roll (0802999), and THERMOMARK-RIBBON 110/50 ink ribbon (0800687) are not included.

Your advantages

- Maximum efficiency: time savings of up to 70% compared to manual printing and application processes
- Consistently high level of efficiency over the entire working day through intuitive handling, which helps reduce costs
- Planning accuracy with regard to productivity and quality: in the case of order peaks, productivity can be increased significantly using the same number of employees
- Reduction in the number of user errors through intuitive step-by-step guidance along the entire identification process as well as automatic data processing from CAE systems and other popular file formats for data exchange
- The continuous format means that one material can cover all wire and cable diameters ranging from 1.8 mm ... 5.6 mm (0.07" ... 0.22"). It is therefore not necessary to change materials
- Easy and efficient handling, as the diameter of the cylindrical object is measured automatically and the size of the marker is optimally adjusted accordingly
- Thanks to the three-sided printing and sliding action of the markers on the wires/cables, the marking is clearly visible once installed
- Due to the triangular shape of the markers, different information can be printed on each of the three marking areas
- The very strong heat-sealed joint ensures that the markers remain captive

THERMOMARK E.WIRE SET US - Applicator set



1287046

<https://www.phoenixcontact.com/us/products/1287046>

- The permanent identification of single-core wires, wires, cables, twisted cable bundles, and other cylindrical objects provides maximum flexibility
- Thanks to the intuitive operating concept and symmetrical structure, the applicator can be used ergonomically by both right- and left-handed users
- Quick and easy mounting of the applicator on the roll printer via hexagon screw
- The applicator is connected via the D-SUB interface on the roll printer and is detected automatically by the software

Commercial data

Item number	1287046
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG01
Product key	BG1222
GTIN	4063151512194
Weight per piece (including packing)	14,931 g
Weight per piece (excluding packing)	12,940 g
Customs tariff number	84433210
Country of origin	DE

THERMOMARK E.WIRE SET US - Applicator set



1287046

<https://www.phoenixcontact.com/us/products/1287046>

Set consists of

THERMOMARK E.WIRE - Applicator

1203216

<https://www.phoenixcontact.com/us/products/1203216>



Applicator for the efficient printing and application of movable E-WM... markers on wires and cables in a single automated process step

THERMOMARK E.300 US - Thermal transfer printer

1287021

<https://www.phoenixcontact.com/us/products/1287021>



Thermal transfer printer for printing all materials in roll format with a print resolution of 300 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

THERMOMARK E.WIRE SET US - Applicator set



1287046

<https://www.phoenixcontact.com/us/products/1287046>

TM E.WIRE/E.SLEEVE-PR - Pressure roller

1259203

<https://www.phoenixcontact.com/us/products/1259203>



Pressure roller for all E-WM... and E-WMS... materials (for material width of up to 30 mm/1.18")

THERMOMARK E.WIRE SET US - Applicator set



1287046

<https://www.phoenixcontact.com/us/products/1287046>

Technical data

Product properties

Product type	Marking system
Scope of supply	THERMOMARK E.WIRE (1203216), TM E.WIRE/E.SLEEVE-PR pressure roller (1259203), THERMOMARK E.300 BASIC, power cable (pin connector pattern: type "F"), USB cable, and multilingual packing slip

Marking

Identification technology	Thermal transfer for rolls
---------------------------	----------------------------

Device properties

Print resolution	300 dpi
Operating system	Windows 10, Windows 11, Windows Server 2016, Windows Server 2019, Windows Server 2022

Dimensions

Width	252 mm
Height	288 mm

THERMOMARK E.WIRE SET US - Applicator set



1287046

<https://www.phoenixcontact.com/us/products/1287046>

Classifications

ECLASS

ECLASS-13.0	19140104
ECLASS-15.0	19140104

ETIM

ETIM 9.0	EC001684
----------	----------

THERMOMARK E.WIRE SET US - Applicator set



1287046

<https://www.phoenixcontact.com/us/products/1287046>

Accessories

THERMOMARK E.CUTTER - Cutter

1234241

<https://www.phoenixcontact.com/us/products/1234241>

Cutter for marking materials in continuous format for cutting custom lengths



THERMOMARK E.CUTTER/P - Cutter

1201336

<https://www.phoenixcontact.com/us/products/1201336>

Perforation cutter for all shrink sleeve and marking sleeve versions in continuous format for cutting custom lengths



THERMOMARK E.WIRE SET US - Applicator set



1287046

<https://www.phoenixcontact.com/us/products/1287046>

TM-RIBBON 30 BK 103 - Ink ribbon

1309076

<https://www.phoenixcontact.com/us/products/1309076>



Ink ribbon, for the E-WM... product group in combination with the THERMOMARK E.WIRE applicator, length: 300 m, roll length: 300 m, width: 30 mm, color: black

TRM-PRESSURE ROLLER STANDARD - Pressure roller

0804655

<https://www.phoenixcontact.com/us/products/0804655>



Standard pressure roller

THERMOMARK E.WIRE SET US - Applicator set



1287046

<https://www.phoenixcontact.com/us/products/1287046>

TRM-PRESSURE ROLLER 4-50 - Pressure roller

0804656

<https://www.phoenixcontact.com/us/products/0804656>



Pressure roller for continuous shrink sleeve

TM E.WIRE/E.SLEEVE-PR - Pressure roller

1259203

<https://www.phoenixcontact.com/us/products/1259203>



Pressure roller for all E-WM... and E-WMS... materials (for material width of up to 30 mm/1.18")

THERMOMARK E.WIRE SET US - Applicator set



1287046

<https://www.phoenixcontact.com/us/products/1287046>

TM E.300/E.600-TEAR OFF PLATE - Demolition plate

1263118

<https://www.phoenixcontact.com/us/products/1263118>

Tear-off plate for all roll printers in the THERMOMARK E SERIES



TM E.300/E.600-FRONT COVER - Front plate

1285305

<https://www.phoenixcontact.com/us/products/1285305>

Front panel for all roll printers in the THERMOMARK E SERIES



THERMOMARK E.WIRE SET US - Applicator set



1287046

<https://www.phoenixcontact.com/us/products/1287046>

TM E.WIRE-CARDBOARD BOX - Original packaging

1371339

<https://www.phoenixcontact.com/us/products/1371339>



Original packaging incl. inlay for safe transportation of the THERMOMARK E. WIRE

MARKING SYSTEM SOFTWARE - Software

1669297

<https://www.phoenixcontact.com/us/products/1669297>



Create marking files easily and conveniently on your laptop or desktop PC. All Phoenix Contact marking systems as well as standard office printers can be controlled via the software. The software is available for download.

THERMOMARK E.WIRE SET US - Applicator set



1287046

<https://www.phoenixcontact.com/us/products/1287046>

PROJECT COMPLETE - Software

1050453

<https://www.phoenixcontact.com/us/products/1050453>



Intuitive planning and marking software for configuring terminal strips and for professional marking of marking materials for terminal blocks, conductors, cables, devices, and systems. The software is available for download

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com