

# MC 1000-MM LC - FO converters



1329819  
<https://www.phoenixcontact.com/us/products/1329819>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fiber optic converter with LC duplex connection (1310 nm) for 100Base-TX to multimode fiber optics, DIN rail mountable.

## Product description

The MC 1000-MM LC media converter comes with one 10/100 Mbps twisted-pair RJ45 port and one 100 Mbps multimode fiber optics port with an LC connector.

## Your advantages

- Auto MDI/MDI-X switch-over
- Data transfer rates of 100 Mbps
- Link fault pass through (LFPT) function for easy connection monitoring

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1329819       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DN06          |
| Product key                          | DNC314        |
| GTIN                                 | 4063151625719 |
| Weight per piece (including packing) | 191.4 g       |
| Weight per piece (excluding packing) | 124 g         |
| Customs tariff number                | 85176200      |
| Country of origin                    | CA            |

# MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/us/products/1329819>

## Technical data

### Notes

#### Note on application

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

#### Utilization restriction

|          |                                                                           |
|----------|---------------------------------------------------------------------------|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---------------------------------------------------------------------------|

### Product properties

|                |                                                                                                            |
|----------------|------------------------------------------------------------------------------------------------------------|
| Product type   | Media converter                                                                                            |
| Product family | MC 1000                                                                                                    |
| MTTF           | 86.4 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)                                |
|                | 756.3 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)                                     |
|                | 370.3 Years (Telcordia standard, temperature 25 °C, operating cycle 100 % (7 days a week, 24 hours a day)) |

### Electrical properties

#### Supply

|                             |                         |
|-----------------------------|-------------------------|
| Supply voltage range        | 12 V DC ... 48 V DC     |
| Nominal supply voltage      | 24 V DC                 |
| Typical current consumption | 20 mA (24 V DC)         |
| Max. current consumption    | 170 mA (12 V DC, 60 °C) |

### Connection data

#### Supply

|                                         |                           |
|-----------------------------------------|---------------------------|
| Connection method                       | Push-in spring connection |
| Single conductor/terminal point, rigid  | 0.2 mm² ... 2.5 mm²       |
| Single-wire/terminal point, flexible    | 0.2 mm² ... 2.5 mm²       |
| Conductor cross-section, flexible [AWG] | 24 ... 12                 |
| Conductor cross-section AWG             | 24 ... 12                 |
| Stripping length                        | 10.00 mm                  |

### Interfaces

|        |          |
|--------|----------|
| Signal | Ethernet |
|--------|----------|

#### Data: optical FO

|                                               |                                             |
|-----------------------------------------------|---------------------------------------------|
| Transmit capacity, minimum                    | -20 dBm (62.5/125 µm, multimode fiberglass) |
|                                               | -23.5 dBm (50/125 µm, multimode fiberglass) |
| Transmit capacity, maximum                    | -14 dBm                                     |
| Transmission length incl. 3 dB system reserve | 2 km                                        |

# MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/us/products/1329819>

|                              |                       |
|------------------------------|-----------------------|
| Connection method            | LC duplex             |
| Wavelength                   | 1310 nm               |
| Minimum receiver sensitivity | -31 dBm               |
| Maximum receiver sensitivity | -8 dBm                |
| Transmission medium          | Multi-mode fiberglass |

Data: Ethernet interface, 100Base-T(X) in accordance with IEEE 802.3

|                        |                                |
|------------------------|--------------------------------|
| Transmission speed     | 10/100 Mbps                    |
| Connection method      | RJ45 jack, shielded            |
| No. of channels        | 1                              |
| Transmission length    | 100 m (twisted pair, shielded) |
| Transmission medium    | Copper                         |
| Signal LEDs            | LNK/ACT, SPD, US               |
| Auto-negotiation modes | Auto                           |
| Link through           | Link fault pass through        |
| MDI-/MDI-X switchover  | Auto-MDI(X)                    |

## Dimensions

|        |         |
|--------|---------|
| Width  | 22.5 mm |
| Height | 123 mm  |
| Depth  | 90 mm   |

## Material specifications

|                    |                                 |
|--------------------|---------------------------------|
| Material (Housing) | Polyamide fiberglass reinforced |
|--------------------|---------------------------------|

## Cable/line

FO cable

|             |             |
|-------------|-------------|
| Fiber types | 50/125 µm   |
|             | 62.5/125 µm |
|             | Fiberglass  |

## Mechanical tests

|                                                                    |                                    |
|--------------------------------------------------------------------|------------------------------------|
| Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6 | : 5g, 150 Hz, Criterion 3          |
| Shock in accordance with EN 60068-2-27/IEC 60068-2-27              | : 30g, 11 ms half-sine shock pulse |

## Environmental and real-life conditions

Ambient conditions

|                                         |                                            |
|-----------------------------------------|--------------------------------------------|
| Degree of protection                    | IP30                                       |
| Ambient temperature (operation)         | -10 °C ... 60 °C                           |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C                           |
| Altitude                                | ≤ 2000 m (in acc. with UL)                 |
| Permissible humidity (operation)        | 10 % ... 95 % (non-condensing)             |
| Shock                                   | 300 m/s <sup>2</sup> , 11 ms (IEC 60068-2) |

# MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/us/products/1329819>

## Approvals

CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

## EMC data

|                               |                                           |
|-------------------------------|-------------------------------------------|
| Electromagnetic compatibility | Conformance with EMC Directive 2014/30/EU |
|-------------------------------|-------------------------------------------|

Electrostatic discharge

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-2 |
|-----------------------|--------------|

Electrostatic discharge

|          |             |
|----------|-------------|
| Comments | Criterion B |
|----------|-------------|

Electromagnetic HF field

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-3 |
|-----------------------|--------------|

Electromagnetic HF field

|          |             |
|----------|-------------|
| Comments | Criterion A |
|----------|-------------|

Fast transients (burst)

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-4 |
|-----------------------|--------------|

Fast transients (burst)

|          |             |
|----------|-------------|
| Comments | Criterion A |
|----------|-------------|

Surge current load (surge)

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-5 |
|-----------------------|--------------|

Surge current load (surge)

|          |             |
|----------|-------------|
| Comments | Criterion B |
|----------|-------------|

Conducted interference

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-6 |
|-----------------------|--------------|

Conducted interference

|          |             |
|----------|-------------|
| Comments | Criterion A |
|----------|-------------|

Emitted interference

|                       |          |
|-----------------------|----------|
| Standards/regulations | EN 55032 |
|-----------------------|----------|

## Mounting

|                       |                                                    |
|-----------------------|----------------------------------------------------|
| Mounting type         | DIN rail mounting                                  |
| Mounting position     | on horizontal DIN rail NS 35 in acc. with EN 60715 |
| Useable DIN rail type | DIN rail: 35 mm                                    |

# MC 1000-MM LC - FO converters

1329819

<https://www.phoenixcontact.com/us/products/1329819>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1329819>



**cULus Listed**

Approval ID: E238705

# MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/us/products/1329819>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 19170411 |
| ECLASS-15.0 | 19170411 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001467 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 43223323 |
|-------------|----------|

# MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/us/products/1329819>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

# MC 1000-MM LC - FO converters



1329819


<https://www.phoenixcontact.com/us/products/1329819>

## Accessories

### FKCT 2,5/ 3-ST KMGY - PCB connector

1998263

<https://www.phoenixcontact.com/us/products/1998263>



PCB connector, nominal cross section: 2.5 mm<sup>2</sup>, color: light gray, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Socket, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: FKCT 2,5/...-ST, pitch: 5 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, locking clip: - Locking clip, plug-in system: COMBICON MSTB 2,5, locking: without, mounting method: without, type of packaging: packed in cardboard

---

### DT-LAN-CAT.6+ - Surge protection device

2881007

<https://www.phoenixcontact.com/us/products/2881007>



Surge protection in accordance with Class E<sub>A</sub> (CAT6<sub>A</sub>), for Gigabit Ethernet (up to 10 Gbps), token ring, FDDI/CDDI, ISDN, DS1. Suitable for Power over Ethernet (PoE++/4PPoE) "Mode A" and "Mode B". RJ45 intermediate plug with separate grounding cable and ground connection snap-on foot for NS 35 DIN rails. Products with similar requirements: DT-LAN-CAT.6A (2908726) und D-LAN-CAT.5-HC (2800763).

# MC 1000-MM LC - FO converters



1329819

<https://www.phoenixcontact.com/us/products/1329819>

## FL DIN-RAIL ADAPTER 22.5 - Mounting panel

1085485

<https://www.phoenixcontact.com/us/products/1085485>



The FL DIN-RAIL ADAPTER 22.5 is designed to allow products 22.5 mm wide to be mounted flush to a standard 35 mm DIN rail, in any orientation.

---

## FL PANEL ADAPTER 22.5 - Mounting panel

1085488

<https://www.phoenixcontact.com/us/products/1085488>



The FL PANEL ADAPTER 22.5 is designed to allow products 22.5 mm wide to be mounted flush to a panel, in any orientation.

# MC 1000-MM LC - FO converters

1329819

<https://www.phoenixcontact.com/us/products/1329819>




## E/NS 35 N - End bracket

0800886

<https://www.phoenixcontact.com/us/products/0800886>

End clamp, width: 9.5 mm, color: gray



---

## FL CAT5 PATCH 0,5 - Patch cable

2832263

<https://www.phoenixcontact.com/us/products/2832263>

Patch cable, CAT5, assembled, 0.5 m



# MC 1000-MM LC - FO converters

1329819

<https://www.phoenixcontact.com/us/products/1329819>



## FL CAT5 PATCH 1,0 - Patch cable

2832276

<https://www.phoenixcontact.com/us/products/2832276>



Patch cable, CAT5, assembled, 1 m

---

## FL CAT5 PATCH 2,0 - Patch cable

2832289

<https://www.phoenixcontact.com/us/products/2832289>



Patch cable, CAT5, assembled, 2 m

# MC 1000-MM LC - FO converters

1329819


<https://www.phoenixcontact.com/us/products/1329819>



## NBC-R4AC-R4AC-IE8A/.../... - Patch cable

1411854

<https://www.phoenixcontact.com/us/products/1411854>




Patch cable, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, cable outlet: straight, Ethernet

---

## NBC-R4AC/10G-R4AC/10G-94F/2,0 - Patch cable

1408360

<https://www.phoenixcontact.com/us/products/1408360>



Patch cable, CAT6<sub>A</sub>, 4-pair, shielded, connection not crossed (line), assembled at both ends with RJ45/IP20 connectors, outer sheath material: PUR, length: 2.0 m

# MC 1000-MM LC - FO converters

1329819


<https://www.phoenixcontact.com/us/products/1329819>



## NBC-R4AC/10G-R4AC/10G-94F/3,0 - Patch cable

1408365

<https://www.phoenixcontact.com/us/products/1408365>



Patch cable, CAT6<sub>A</sub>, 4-pair, shielded, connection not crossed (line), assembled at both ends with RJ45/IP20 connectors, outer sheath material: PUR, length: 3.0 m

---

## SZS 0,4X2,0 - Screwdriver

1205202

<https://www.phoenixcontact.com/us/products/1205202>



Micro screwdriver, bladed, size: 0.4 x 2.0 x 60 mm, 2-component grip, with non-slip grip and twist cap

# MC 1000-MM LC - FO converters

1329819

<https://www.phoenixcontact.com/us/products/1329819>



## FL DIN RA - DIN rail adapter

2891053

<https://www.phoenixcontact.com/us/products/2891053>

The FL DIN RA is installed in a standard, 19-inch rack (EIA-310-D, IEC 60297-3-100) to allow DIN rail mounted equipment to be rack mounted.



---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)