

NBC-R4AQ/30,0-971/R4AQ VR - Network cable



1412817

<https://www.phoenixcontact.com/us/products/1412817>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled VARAN cable, shielded, stranded, black, RJ45 plug/IP20, QUICKON to RJ45 plug/IP20, QUICKON, length: 30 m

Commercial data

Item number	1412817
Packing unit	1 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ABNABA
GTIN	4055626017501
Weight per piece (including packing)	2,115 g
Weight per piece (excluding packing)	2,115 g
Country of origin	DE

1412817

<https://www.phoenixcontact.com/us/products/1412817>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	VARAN
Number of positions	6
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Overvoltage category	I
Degree of pollution	1

Electrical properties

Rated voltage (III/3)	72 V (DC)
Contact resistance	$\leq 5 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V
Nominal current I_N	2 A
Transmission speed	100 Mbps

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Material specifications

Color	black
Material	PC
	PA
Flammability rating according to UL 94	V0
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated
Outer sheath, material	SANTOPRENE halogen-free

Connector

Connection 2

Type	Plug straight RJ45
Degree of protection	IP20
	IP20

NBC-R4AQ/30,0-971/R4AQ VR - Network cable



1412817

<https://www.phoenixcontact.com/us/products/1412817>

Cable/line

Cable length	30.00 m
VARAN PVC [971]	
Shielded	yes
UL AWM Style	2461 (80°C/300 V)
Cable type	VARAN PVC
Cable type (abbreviation)	971
Signal type/category	VARAN CAT5 (IEC 11801), 100 Mbps
Cable structure	1x2x24/32+2x2x24/19, SF/UTP
External cable diameter	7.00 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black
Thickness, outer sheath	0.90 mm
Conductor material	Bare Cu litz wires
Conductor structure signal line	19x 0.13 mm
AWG signal line	24
Conductor structure, voltage supply	32x 0.10 mm
Conductor cross section	2x 2x 0.25 mm² (Signal line)
AWG power supply	24
Material wire insulation	PE
Wire diameter incl. insulation	1.25 mm (Signal line)
	1.4 mm (Power supply)
Single wire, color	blue-yellow, green-orange, red-blue
Twisted pairs	2 cores to the pair
Overall twist	3 pairs with filler elements to the core
Shielding	Aluminum-coated foil, tinned copper braided shield
Optical shield covering	85 %
Nominal voltage, cable	≤ 80 V
Test voltage Core/Core	1000 V
Test voltage Core/Shield	1000.00 V
Cable resistance	78 Ω/km (at 20 °C)
Cable insulation resistance	≥ 500 MΩ*km (at 20 °C)
Working capacitance	approx. 57 nF (at 1 kHz)
Signal runtime	5.3 ns/m
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Number of bending cycles	200000
Minimum bending radius, drag chain applications	5 x D
Resistance to oil	According to DIN EN 60811-2-1, 168 h at 100°C
Flame resistance	according to IEC 60332-1-2
Ambient temperature (operation)	-40 °C ... 80 °C

Environmental and real-life conditions

NBC-R4AQ/30,0-971/R4AQ VR - Network cable



1412817

<https://www.phoenixcontact.com/us/products/1412817>

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation) (Cable, fixed installation)	0 °C ... 50 °C (for installation)
	-20 °C ... 80 °C (cable, fixed installation)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)

NBC-R4AQ/30,0-971/R4AQ VR - Network cable


1412817

<https://www.phoenixcontact.com/us/products/1412817>



Drawings

Schematic diagram



Classifications

ECLASS

ECLASS-13.0	27060307
-------------	----------

UNSPSC

UNSPSC 21.0	26121604
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com