

VS-M12MRD-OE-93E/5,0 SKS - Network cable



1448616

<https://www.phoenixcontact.com/us/products/1448616>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet CAT5, 4-position, PUR halogen-free, water blue RAL 5021, shielded, Plug angled M12, coding: D, on free cable end, cable length: 5 m

Commercial data

Item number	1448616
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF04
Product key	AF1CJI
GTIN	4046356703000
Weight per piece (including packing)	232.8 g
Weight per piece (excluding packing)	232.8 g
Customs tariff number	85444290
Country of origin	PL

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	Ethernet
Number of positions	4
No. of cable outlets	1
Shielded	yes
Coding	D

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Interfaces

Bus system	Ethernet
Signal type/category	Ethernet CAT5 (IEC 11801:2002)

Signaling

Status display	no
Status display present	no

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A (Plug/socket in accordance with IEC 61076-2-101, cable technical data is to be observed)
Transmission medium	Copper
Transmission characteristics (category)	CAT5 (IEC 11801:2002)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Connection 1

Type	Plug angled M12
Coding type	D (Data)
Material	CuZn (Contact)
	Ni/Au (Contact surface)
	TPU GF (Contact carrier)

VS-M12MRD-OE-93E/5,0 SKS - Network cable



1448616

<https://www.phoenixcontact.com/us/products/1448616>

	TPU, hardly inflammable, self-extinguishing (Grip body)
	Zinc die-cast, nickel-plated (Screw connection)


Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	5 m
--------------	-----

Ethernet flexible CAT5, 2-pair [93E]

Dimensional drawing		
UL AWM Style	21238 (80 °C / 600 V)	
Number of positions	4	
Shielded	yes	
Cable type	Ethernet flexible CAT5, 2-pair [93E]	
Conductor structure	2x2xAWG26/7, SF/UTP	
AWG signal line	26	
Conductor cross section	2x 2x 0.14 mm ²	
Wire diameter incl. insulation	0.95 mm ±0.05 mm	
External cable diameter	6.40 mm ±0.2 mm	
Outer sheath, material	PUR	
External sheath, color	water blue RAL 5021	
Conductor material	Bare Cu litz wires	
Material wire insulation	Foamed PE	
Single wire, color	white/orange-orange, white/green-green	
Twisted pairs	2 cores to the pair	
Overall twist	Two pairs with two fillers to the core	
Optical shield covering	70 %	
Insulation resistance	≥ 5 GΩ*km	
Loop resistance	≤ 280.00 Ω/km	
Wave impedance	100 Ω ±5 Ω (at 100 MHz)	
Nominal voltage, cable	≤ 100 V	
Test voltage Core/Core	2000 V (50 Hz, 1 min.)	
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)	
Minimum bending radius, fixed installation	4 x D	
Minimum bending radius, flexible installation	8 x D	
Smallest bending radius, fixed installation	26 mm	
Smallest bending radius, movable installation	51 mm	

VS-M12MRD-OE-93E/5,0 SKS - Network cable



1448616

<https://www.phoenixcontact.com/us/products/1448616>

Halogen-free	according to IEC 60754-1
Flame resistance	according to IEC 60332-1-2
	in accordance with UN ECE-R 118.03
	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1)
	UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)
Resistance to oil	in accordance with IEC 60811-404
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-30 °C ... 70 °C (Cable, flexible installation)


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP65/IP67/IP69K
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)


Drawings

Dimensional drawing



M12 x 1 male plug, angled, shielded

Schematic diagram




Pin assignment M12 male connector, 4-pos., D-coded, male side

1448616

<https://www.phoenixcontact.com/us/products/1448616>

Circuit diagram



Contact assignment of the M12 plug

VS-M12MRD-OE-93E/5,0 SKS - Network cable



1448616

<https://www.phoenixcontact.com/us/products/1448616>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121604
-------------	----------

VS-M12MRD-OE-93E/5,0 SKS - Network cable



1448616

<https://www.phoenixcontact.com/us/products/1448616>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com