

SAC-4P-M 8MS-M12FS - Adapter



1519736

<https://www.phoenixcontact.com/us/products/1519736>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Adapter, 4-position, Plug straight M8, coding: A, on Socket straight M12, coding: A

Commercial data

Item number	1519736
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BF10
Product key	AF1GBA
GTIN	4046356019927
Weight per piece (including packing)	15.61 g
Weight per piece (excluding packing)	11.95 g
Customs tariff number	85366990
Country of origin	DE

SAC-4P-M 8MS-M12FS - Adapter

1519736

<https://www.phoenixcontact.com/us/products/1519736>



Technical data

Product properties

Product type	M8/M12 adapters
Number of positions	4
No. of cable outlets	1
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3


Electrical properties

Insulation resistance	$\geq 100\text{ M}\Omega$
Nominal voltage U_N	30 V AC
	30 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Dimensions

Dimensional drawing	
Width	17 mm
Height	14.8 mm
Length	52.7 mm

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Connector

Connection 1

Type	Plug straight M8
------	------------------

SAC-4P-M 8MS-M12FS - Adapter



1519736

<https://www.phoenixcontact.com/us/products/1519736>

Number of positions	4
Coding type	A

Connection 2

Type	Socket straight M12
Number of positions	4
Coding type	A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

M8

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104

SAC-4P-M 8MS-M12FS - Adapter


1519736

<https://www.phoenixcontact.com/us/products/1519736>




Drawings

Dimensional drawing



M8/M12 adapter

Schematic diagram



Pin assignment M8 plug, 4-pos., view male side


SAC-4P-M 8MS-M12FS - Adapter

1519736

<https://www.phoenixcontact.com/us/products/1519736>



Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

Schematic diagram




Layout of connector pin assignments

SAC-4P-M 8MS-M12FS - Adapter

1519736

<https://www.phoenixcontact.com/us/products/1519736>

Circuit diagram



Contact assignment of the M8/M12 adapter

SAC-4P-M 8MS-M12FS - Adapter



1519736

<https://www.phoenixcontact.com/us/products/1519736>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1519736>



EAC

Approval ID: RU C-DE.AI30.B.01102



UL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	4 A	-	-



cUL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	4 A	-	-

SAC-4P-M 8MS-M12FS - Adapter



1519736

<https://www.phoenixcontact.com/us/products/1519736>

Classifications

ECLASS

ECLASS-13.0	27440106
ECLASS-15.0	27440106

ETIM

ETIM 9.0	EC002925
----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SAC-4P-M 8MS-M12FS - Adapter



1519736
<https://www.phoenixcontact.com/us/products/1519736>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.097 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com