

M23-17P1N8A8002 - Cable connector



1629203

<https://www.phoenixcontact.com/us/products/1629203>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: M23 PRO, straight, shielded: yes, Screw locking mechanism, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 4 mm ... 8.5 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Solutions with cross-manufacturer compatibility for standard and fast locking systems
- Reliable under the harshest conditions: cable connectors with vibration brake
- Modern, consistent design for highly convenient operation
- Easy, cost-effective cable assembly: uniform shielding of M17 to M40

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1629203 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | AB30 |
| Product key | ABRABA |
| GTIN | 4055626618364 |
| Weight per piece (including packing) | 116.3 g |
| Weight per piece (excluding packing) | 100.605 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

M23-17P1N8A8002 - Cable connector



1629203

<https://www.phoenixcontact.com/us/products/1629203>

Technical data

Notes

| | |
|--------------------|--|
| Order information: | Order 17 x 1 mm crimp contacts separately |
| Safety note | |
| Safety note | <p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none">• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.• The products are suitable for applications in plant, controller, and electrical device engineering.• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.• Assembled products may not be manipulated or improperly opened.• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).• When using the product in direct connection with third-party manufacturers, the user is responsible.• For operating voltages > 50 V AC, conductive connector housings must be grounded• Ensure that the protective or functional ground has been properly connected.• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector• Only use tools recommended by Phoenix Contact• The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.• Operate the connector only when it is fully plugged in and interlocked.• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.• Observe the minimum bending radius of the cable. Lay the cable without twisting it.• The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting |

M23-17P1N8A8002 - Cable connector



1629203

<https://www.phoenixcontact.com/us/products/1629203>

warnings (e.g. DIN EN ISO 13732-1:2008-12).

Product properties

| | |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

Connector

Insulating body

| | |
|--|--|
| Note | Order information: Order 17 x 1 mm crimp contacts separately |
| Coding | N |
| Material (Insulating body) | PA 6.6 |
| Insertion/withdrawal cycles | 100 |
| Connection method | Crimp connection |
| Contact switching type | Pin |
| Application | Signal |
| Number of positions | 17 |
| Direction of rotation | Standard |
| Connection profile | 17 |
| Installation height | 2000 m |
| Number Contact (Signal contacts) | 17 |
| Diameter Contact (Signal contacts) | 1 mm |
| Litz wire cross-section min. Contact (Signal contacts) | 0.08 mm ² |
| Litz wire cross-section max. Contact (Signal contacts) | 1 mm ² |
| Rated current Contact (Signal contacts) | 8 A (for max. connection cross section) |
| Rated voltage Contact (Signal contacts) | 125 V |
| Rated surge voltage | 2 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |

Housing

| | |
|-----------------------------------|------------------------------|
| Type | Cable connector housing |
| Thread type | M23 |
| Design | straight |
| Type of locking | Screw locking mechanism |
| Pg screw connection | none |
| Housing material | GD-Zn |
| Degree of protection (plugged in) | IP66/IP68 (2 m / 24 h) IP69K |

Seal

| | |
|-------------------------|-----------------|
| External cable diameter | 4 mm ... 8.5 mm |
| Seal material | FKM |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------------------------|
| Ambient temperature (operation) | -40 °C ... 105 °C (see to derating) |
|---------------------------------|-------------------------------------|

M23-17P1N8A8002 - Cable connector



1629203

<https://www.phoenixcontact.com/us/products/1629203>

| | |
|-----------------------|------------------------------------|
| Permanent temperature | 125 °C (DIN EN 60512-9-2 / 1000 h) |
|-----------------------|------------------------------------|

M23-17P1N8A8002 - Cable connector


1629203

<https://www.phoenixcontact.com/us/products/1629203>



Drawings

Dimensional drawing



Dimensional drawing, housing


M23-17P1N8A8002 - Cable connector

1629203

<https://www.phoenixcontact.com/us/products/1629203>



Schematic diagram



Connector pin assignment


M23-17P1N8A8002 - Cable connector

1629203

<https://www.phoenixcontact.com/us/products/1629203>



Schematic diagram




Connector pin assignment

M23-17P1N8A8002 - Cable connector

1629203

<https://www.phoenixcontact.com/us/products/1629203>



I = current strength, ϑ = ambient temperature, 17x 6 A

M23-17P1N8A8002 - Cable connector





1629203

<https://www.phoenixcontact.com/us/products/1629203>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1629203>

|  cUL Recognized Approval ID: E335019-20141210 | | | | |
|--|--------------------------------|--------------------------------|-------------------|-------------------------------|
| | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| keine | | | | |
| | 150 V | 3.5 A | 20 | - |

|  UL Recognized Approval ID: E335019-20141210 | | | | |
|---|--------------------------------|--------------------------------|-------------------|-------------------------------|
| | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| keine | | | | |
| | 150 V | 4.5 A | 20 | - |

M23-17P1N8A8002 - Cable connector



1629203

<https://www.phoenixcontact.com/us/products/1629203>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

M23-17P1N8A8002 - Cable connector



1629203

<https://www.phoenixcontact.com/us/products/1629203>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com