

HC-K12/ 2-EBUC - Contact insert

1636347

<https://www.phoenixcontact.com/us/products/1636347>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 12+2+PE, size: B16, power contacts: 12, control contacts: 2, Socket, Crimp connection, 690 V, 40 A, 1.5 mm² ... 6 mm², application: Power/signal

Your advantages

- Shock and vibration-resistant in accordance with DIN EN 61373

Commercial data

Item number	1636347
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF61
Product key	AF7ABA
GTIN	4046356011488
Weight per piece (including packing)	87 g
Weight per piece (excluding packing)	83.8 g
Customs tariff number	85366990
Country of origin	CN

HC-K12/ 2-EBUC - Contact insert

1636347

<https://www.phoenixcontact.com/us/products/1636347>



Technical data

Notes

General	For HEAVYCON ADVANCE and HEAVYCON housing of type B16/B32, power contacts: CK 4,0-ED, control contacts: CK 1,6-ED (crimp contacts not supplied as standard)
General	Connectors may be operated only when there is no load/voltage.

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---

Product properties

Product type	Contact insert with a fixed no. of positions
Series	HC-K
Application	Power/signal
Type	B16
	B32
Number of positions	14
Connection profile	12+2+PE
Contact numbering	1 - 12 (power contacts) 1 - 2 (control contacts)
No. of power contacts	12
No. of control contacts	2
Contact material type	turned

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Dimensions

Dimensional drawing	
Width	34 mm
Height	41.5 mm
Length	84.5 mm
Drill hole distance, horizontal	77.5 mm

Mechanical characteristics

Contact diameter	4 mm
------------------	------

Connection data

HC-K12/ 2-EBUC - Contact insert

1636347

<https://www.phoenixcontact.com/us/products/1636347>



Connection technology

Connection technology	Crimp connection (power contacts) Crimp connection (control contacts)
-----------------------	--

Conductor connection

Conductor cross section	1.5 mm ² ... 6 mm ² (power contacts) 0.14 mm ² ... 2.5 mm ² (control contact)
Connection cross section AWG	16 ... 10 (power contacts) 26 ... 14 (control contacts)
Tightening torque	0.8 Nm ... 1.2 Nm (PE connection) 0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the HEAVYCON housing)
Stripping length of the individual wire	9 mm (Power 1.5 mm ² ... 2.5 mm ²) 8 mm (Control contacts, with a cross section of 0.14 mm ² ... 1.5 mm ²) 9.5 mm (power contacts, with a cross section of 4 mm ² ... 6 mm ²) 6 mm (Control contacts, with a cross section of 2.5 mm ²)

Electrical properties

Rated voltage (III/3)	690 V (power contacts) 250 V (control contacts)
Rated surge voltage	8 kV (power contacts) 4 kV (control contacts)
Rated current	40 A (power contacts) 10 A (control contacts)

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

Material specifications

Flammability rating according to UL 94	V0
Contact material	Cu alloy
Contact carrier material	PC
Material of contact surface, power contact	Ag
Material of contact surface, control contact	Ag (alternatively Au)
Standards/regulations	PC
	PC

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation) (Operation)	-40 °C ... 125 °C (including heating up of contacts)

Standards and regulations

HC-K12/ 2-EBUC - Contact insert

1636347

<https://www.phoenixcontact.com/us/products/1636347>



Testing

Standards/regulations	PC: Fire protection in rail vehicles - requirement set R22 acc. to DIN EN 45545-2 (Risk level HL1 - HL2)
	PC: Fire protection in rail vehicles - requirement set R23 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)

HC-K12/ 2-EBUC - Contact insert




1636347

<https://www.phoenixcontact.com/us/products/1636347>


Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing



Mounting cutout when used without housing


HC-K12/ 2-EBUC - Contact insert

1636347

<https://www.phoenixcontact.com/us/products/1636347>



Schematic diagram



Connector pin assignment, connection side


HC-K12/ 2-EBUC - Contact insert

1636347

<https://www.phoenixcontact.com/us/products/1636347>



Diagram



Derating diagram

HC-K12/ 2-EBUC - Contact insert

1636347

<https://www.phoenixcontact.com/us/products/1636347>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1636347>

UL Recognized				
Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
Power	600 V	40 A	- 10	-
Control	600 V	10 A	14	-

HC-K12/ 2-EBUC - Contact insert

1636347

<https://www.phoenixcontact.com/us/products/1636347>



Classifications

ECLASS

ECLASS-13.0	27440205
ECLASS-15.0	27440205

ETIM

ETIM 9.0	EC000438
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

HC-K12/ 2-EBUC - Contact insert

1636347

<https://www.phoenixcontact.com/us/products/1636347>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	6.812 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com