

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Knife-disconnect terminal block, With test socket screws for insertion of test plugs, nom. voltage: 500 V, nominal current: 20 A, number of connections: 3, connection method: Screw connection, Rated cross section: 4 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup> - 6 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: gray

Your advantages

- Compact design and high current carrying capacity of 20 A
- Double bridge shaft enables individual potential distribution and supply

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3064014       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE01          |
| Product key                          | BE1131        |
| GTIN                                 | 4046356285988 |
| Weight per piece (including packing) | 16.072 g      |
| Weight per piece (excluding packing) | 16.072 g      |
| Customs tariff number                | 85369010      |
| Country of origin                    | PL            |

# UT 4-TWIN-MT P/P - Knife-disconnect terminal block



3064014

<https://www.phoenixcontact.com/us/products/3064014>

## Technical data

### Product properties

|                       |                           |
|-----------------------|---------------------------|
| Product type          | Disconnect terminal block |
| Product family        | UT                        |
| Number of connections | 3                         |
| Number of rows        | 1                         |
| Potentials            | 1                         |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                                                 |        |
|-------------------------------------------------|--------|
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 1.02 W |

### Connection data

|                                 |                   |
|---------------------------------|-------------------|
| Number of connections per level | 3                 |
| Nominal cross section           | 4 mm <sup>2</sup> |

### Level 1 above 1 below 1

|                                                                                           |                                                       |
|-------------------------------------------------------------------------------------------|-------------------------------------------------------|
| Connection method                                                                         | Screw connection                                      |
| Screw thread                                                                              | M3                                                    |
| Tightening torque                                                                         | 0.6 ... 0.8 Nm                                        |
| Stripping length                                                                          | 9 mm                                                  |
| Internal cylindrical gage                                                                 | A4                                                    |
| Connection in acc. with standard                                                          | IEC 60947-7-1                                         |
| Conductor cross-section rigid                                                             | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>            |
| Cross section AWG                                                                         | 26 ... 10 (converted acc. to IEC)                     |
| Conductor cross-section flexible                                                          | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>            |
| Conductor cross-section, flexible [AWG]                                                   | 26 ... 10 (converted acc. to IEC)                     |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>            |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>            |
| 2 conductors with same cross section, solid                                               | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>          |
| 2 conductors with same cross section, flexible                                            | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>          |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>          |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>           |
| Nominal current                                                                           | 20 A (with 6 mm <sup>2</sup> conductor cross-section) |
| Maximum load current                                                                      | 20 A (with 6 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage                                                                           | 500 V                                                 |
| Nominal cross section                                                                     | 4 mm <sup>2</sup>                                     |

# UT 4-TWIN-MT P/P - Knife-disconnect terminal block



3064014

<https://www.phoenixcontact.com/us/products/3064014>

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 6.2 mm  |
| End cover width    | 2.2 mm  |
| Height             | 65.4 mm |
| Depth on NS 35/7,5 | 49.1 mm |
| Depth on NS 35/15  | 56.6 mm |

## Material specifications

|                                                                  |                 |
|------------------------------------------------------------------|-----------------|
| Color                                                            | gray (RAL 7042) |
| Flammability rating according to UL 94                           | V0              |
| Insulating material group                                        | I               |
| Insulating material                                              | PA              |
| Static insulating material application in cold                   | -60 °C          |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26           | HL 1 - HL 3     |
| Surface flammability NFPA 130 (ASTM E 162)                       | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)          | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                           | passed          |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

### Ambient conditions

|                                          |                                                                                                                              |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)                                                    |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                                                                              |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                                                                              |
| Permissible humidity (operation)         | 20 % ... 90 %                                                                                                                |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                                                                                |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# UT 4-TWIN-MT P/P - Knife-disconnect terminal block




3064014

<https://www.phoenixcontact.com/us/products/3064014>

## Drawings

Circuit diagram



# UT 4-TWIN-MT P/P - Knife-disconnect terminal block



3064014

<https://www.phoenixcontact.com/us/products/3064014>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3064014>

|  <b>IECEE CB Scheme</b><br>Approval ID: DE1-62910 |                       |                       |                   |                             |
|------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                    | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                              |                       |                       |                   |                             |
|                                                                                                                                    | 500 V                 | 20 A                  | -                 | 0.2 - 4                     |

|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                             |
|----------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                                |                       |                       |                   |                             |
|                                                                                                                                  | 300 V                 | 16 A                  | 26 - 10           | -                           |
| Multi-conductor connection                                                                                                       | 300 V                 | 16 A                  | 26 - 14           | -                           |
| C                                                                                                                                |                       |                       |                   |                             |
|                                                                                                                                  | 150 V                 | 16 A                  | 26 - 10           | -                           |
| D                                                                                                                                |                       |                       |                   |                             |
|                                                                                                                                  | 300 V                 | 10 A                  | 26 - 10           | -                           |

|  <b>VDE Zeichengenehmigung</b><br>Approval ID: 40041930 |                       |                       |                   |                             |
|--------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                            | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                                      |                       |                       |                   |                             |
|                                                                                                                                            | 500 V                 | 20 A                  | -                 | 0.2 - 4                     |

|  <b>EAC</b><br>Approval ID: KZ7500651131219505 |  |  |  |  |
|-----------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
|-----------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|

# UT 4-TWIN-MT P/P - Knife-disconnect terminal block



3064014

<https://www.phoenixcontact.com/us/products/3064014>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250108 |
| ECLASS-15.0 | 27250108 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000902 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UT 4-TWIN-MT P/P - Knife-disconnect terminal block



3064014

<https://www.phoenixcontact.com/us/products/3064014>

## Environmental product compliance

### EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 3d9ecbdf-7829-4783-9e49-c53f8b7e4caf |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)