

US-EMP (60X15) YE CUS - Snap-in markers



0830053

<https://www.phoenixcontact.com/us/products/0830053>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Snap-in markers, Card, can be ordered: by card, yellow, labeled according to customer specifications, mounting type: snapped into marker carrier, Number of individual labels: 9, text field height: 15 mm, text field width: 60 mm



Your advantages

- All US-EMP ... device markers can also be supplied labeled according to customer requirements

Commercial data

Item number	0830053
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8149
GTIN	4046356614153
Weight per piece (including packing)	15.844 g
Weight per piece (excluding packing)	15.71 g
Country of origin	PL

US-EMP (60X15) YE CUS - Snap-in markers



0830053

<https://www.phoenixcontact.com/us/products/0830053>

Technical data

Product properties

Product type	Gerätemarker
--------------	--------------

Marking

Number of individual labels	9
Number of individual labels per row	1
Identification technology	Thermal transfer for sheets and cards

Dimensions

Width	59.70 mm
Height	14.90 mm
Depth	0.50 mm
Length	14.9 mm

Material specifications

RoHS compliant	yes
Foil strength	500 µm
Color	yellow (RAL 1018)
Material	PVC
	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10 ... 25 °C / 35 ... 65 % relative humidity. Storage in a cool and dry place is recommended.
Recommended ambient temperature (storage/transport)	10 °C ... 25 °C
Recommended humidity (storage/transport)	35 % ... 65 %
Shelf life	12 months (see packaging date)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

US-EMP (60X15) YE CUS - Snap-in markers



0830053

<https://www.phoenixcontact.com/us/products/0830053>

Mounting

Mounting type	snapped into marker carrier
---------------	-----------------------------

US-EMP (60X15) YE CUS - Snap-in markers



0830053

<https://www.phoenixcontact.com/us/products/0830053>

Classifications

ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

US-EMP (60X15) YE CUS - Snap-in markers



0830053

<https://www.phoenixcontact.com/us/products/0830053>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com