

PTFIX 1,5-NS35 - DIN rail adapter



1049497

<https://www.phoenixcontact.com/us/products/1049497>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail adapter, for NS 35 and NS 15 for accommodating 1.5 mm² FIX blocks in vertical direction, color: gray



Commercial data

Item number	1049497
Packing unit	30 pc
Minimum order quantity	30 pc
Sales key	BE09
Product key	BEAZ11
GTIN	4055626661513
Weight per piece (including packing)	3.733 g
Weight per piece (excluding packing)	3.597 g
Customs tariff number	39269097
Country of origin	PL

PTFIX 1,5-NS35 - DIN rail adapter



1049497

<https://www.phoenixcontact.com/us/products/1049497>

Technical data

Notes

Assembly note	for NS 35 and NS 15 for accommodating 1.5 mm ² FIX blocks in the vertical direction
---------------	--

Product properties

Product type	Mounting material
--------------	-------------------

Dimensions

Width	21.6 mm
Height	58.1 mm
Depth	11 mm

Material specifications

Flammability rating according to UL 94	V0
--	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

PTFIX 1,5-NS35 - DIN rail adapter



1049497

<https://www.phoenixcontact.com/us/products/1049497>

Classifications

ECLASS

ECLASS-13.0	27370419
ECLASS-15.0	27370419

ETIM

ETIM 9.0	EC001024
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PTFIX 1,5-NS35 - DIN rail adapter



1049497
<https://www.phoenixcontact.com/us/products/1049497>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com