

FL SWITCH 1116T - Industrial Ethernet Switch



1085115

<https://www.phoenixcontact.com/us/products/1085115>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ethernet switch, sixteen RJ45 ports with 10/100/1000 Mbps on all ports, wide temperature range, automatic data transmission speed detection, autocrossing function, and QoS

Your advantages

- Auto negotiation and autocrossing detection simplifies installation and setup
- Local diagnostic indicators with LEDs
- RJ45 ports support a transmission speed of 10/100/1000 Mbps
- QoS-prioritized (Quality of Service) messages
- PROFINET Conformance Class A for real-time data exchange
- Energy-efficient Ethernet in accord. with IEEE 802.3az
- PROFINET PTCP filter for reliable communication on PROFINET networks
- Enhanced traffic prioritization for automation protocols
- Jumbo frame support (frame size up to 9216 bytes/frame)

Commercial data

Item number	1085115
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN20
Product key	DNN116
GTIN	4055626834603
Weight per piece (including packing)	736.4 g
Weight per piece (excluding packing)	631 g
Customs tariff number	85176200
Country of origin	TW

FL SWITCH 1116T - Industrial Ethernet Switch



1085115

<https://www.phoenixcontact.com/us/products/1085115>

Technical data

Dimensions

Width	65 mm
Height	141 mm
Depth	107 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Material specifications

Housing material	Polycarbonate fiber reinforced
	Aluminum / steel sheet DC01

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Interfaces

Ethernet (RJ45)

Number of interfaces	16
Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100/1000 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
No. of channels	16 (RJ45 ports)
Input buffer	4.1 Mbits
Output buffer	4.1 Mbits

Product properties

Product type	Switch
Product family	Unmanaged Switch 1000
MTTF	31.4 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
	449.8 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	300.4 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))
Special properties	Extended temperature range
Basic functions	Unmanaged switch
	Autonegotiation
	Store and Forward switching mode

FL SWITCH 1116T - Industrial Ethernet Switch



1085115

<https://www.phoenixcontact.com/us/products/1085115>

Switch functions

Basic functions	Unmanaged switch
	Autonegotiation
	Store and Forward switching mode
MAC address table	8k
Status and diagnostic indicators	LEDs: U _S , link and activity per port
Additional functions	100 BASE-TX/100BASE-FX (IEEE 802.3u)
	Jumbo frames (Max. 9,216 bytes)
	Quality of Service (QoS) prioritization (IEEE 802.1p)
	Energy-efficient Ethernet (IEEE 802.3az)
	Gigabit Ethernet 1000BASE-T (IEEE 802.3ab)
	10Base-T (IEEE 802.3)

Security functions

Basic functions	Unmanaged switch
	Autonegotiation
	Store and Forward switching mode

Electrical properties

Maximum power dissipation for nominal condition	8.55 W (at 24 V DC)
Transmission medium	Copper

Supply

Supply voltage (DC)	24 V DC
Supply voltage (AC)	24 V AC (50/60 Hz)
Supply voltage range	9 V DC ... 32 V DC
	18 V AC ... 30 V AC (50/60 Hz)
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm ²
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Max. current consumption	950 mA (at 9 V DC)
Typical current consumption	91 mA (at 24 V DC)

Connection data

Connection technology

Connection name	Power supply
pluggable	yes

Power supply

Connection method	Push-in spring connection
Conductor cross-section, rigid	0.5 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.5 mm ² ... 2.5 mm ²
Conductor cross-section AWG	20 ... 12
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.5 mm ² ... 2.5 mm ²
Conductor cross-section flexible, with ferrule without plastic sleeve	0.5 mm ² ... 2.5 mm ²

FL SWITCH 1116T - Industrial Ethernet Switch



1085115

<https://www.phoenixcontact.com/us/products/1085115>

Stripping length	10 mm
------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	2000 m (maximum)
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock (operation)	30g (EN 60068-2-27)
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz
Air pressure (operation)	79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating)
Air pressure (storage/transport)	79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating)

Approvals

UL, USA/Canada

Identification	UL 61010-2-201
	UL 61010-1
	Class I, Div. 2 Groups A, B, C, D T4
	Class I, Zone 2, Group IIC T4

ATEX

Identification	Ex II 3G Ex ec IIC T4 Gc
Certificate	UL 22ATEX2910X

IECEX

Identification	Ex ec IIC T4 Gc
Certificate	IECEX UL 22.0104X

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Conformance with EMC directives	EN 61000-6-2 EN 61000-4-2 (ESD) Criterion B
	EN 61000-6-2 EN 61000-4-3 (electromagnetic fields) Criterion A
	EN 61000-6-2 EN 61000-4-4 (EFT burst) Criterion A
	EN 61000-6-2 EN 61000-4-5 (surge) Criterion B
	EN 61000-6-2 EN 61000-4-6 (line noise immunity) Criterion A
	EN 61000-6-2 EN 61000-4-8 (electromagnetic fields) Criterion A
	EN 61000-6-2 Class A
Noise immunity	EN 61000-6-2:2019

Noise emission

Standards/regulations	EN_61000-6-4:2019
-----------------------	-------------------

FL SWITCH 1116T - Industrial Ethernet Switch



1085115

<https://www.phoenixcontact.com/us/products/1085115>

System properties

Functionality	
Basic functions	Unmanaged switch
	Autonegotiation
	Store and Forward switching mode

Signaling

Status display	LEDs: U _S , link and activity per port
----------------	---

FL SWITCH 1116T - Industrial Ethernet Switch



1085115

<https://www.phoenixcontact.com/us/products/1085115>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1085115>

 **KC**
Approval ID: R-R-PCK-1085115

 **DNV GL**
Approval ID: TAA000034U

 **cULus Listed**
Approval ID: E238705

 **IECEx**
Approval ID: IECEx UL 22.0104X

 **ATEX**
Approval ID: UL 22 ATEX 2910X

 **cUL Listed**
Approval ID: E196811

 **UL Listed**
Approval ID: E196811

FL SWITCH 1116T - Industrial Ethernet Switch



1085115

<https://www.phoenixcontact.com/us/products/1085115>

Classifications

ECLASS

ECLASS-13.0	19170402
ECLASS-15.0	19170402

ETIM

ETIM 9.0	EC000734
----------	----------

UNSPSC

UNSPSC 21.0	43222612
-------------	----------

FL SWITCH 1116T - Industrial Ethernet Switch



1085115

<https://www.phoenixcontact.com/us/products/1085115>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	15(a), 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com