


# PCV 5/ 6-GF-15,24 - PCB header



1392190

<https://www.phoenixcontact.com/us/products/1392190>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB headers, nominal cross section: 6 mm<sup>2</sup>, color: green, nominal current: 32 A, rated voltage (III/2): 1000 V, contact surface: Sn, contact connection type: Pin, number of rows: 1, number of positions: 6, product range: PCV 5/..-GF, pitch: 15.24 mm, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 5 mm, number of solder pins per potential: 3, plug-in system: COMBICON PC 5, Pin connector pattern alignment: Standard, locking: Screw locking mechanism, mounting method: Threaded flange, type of packaging: packed in cardboard

## Your advantages

- Well-known mounting principle allows worldwide use
- Screwable flange for superior mechanical stability
- Maximum flexibility when it comes to device design – one header for connectors with different connection technologies

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1392190                        |
| Packing unit                         | 50 pc                          |
| Minimum order quantity               | 50 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AA04                           |
| Product key                          | AADSBD                         |
| GTIN                                 | 4063151773526                  |
| Weight per piece (including packing) | 2.22 g                         |
| Weight per piece (excluding packing) | 2.22 g                         |
| Customs tariff number                | 85366930                       |
| Country of origin                    | PL                             |

# PCV 5/ 6-GF-15,24 - PCB header



1392190

<https://www.phoenixcontact.com/us/products/1392190>

## Technical data

### Product properties

|                           |                       |
|---------------------------|-----------------------|
| Product type              | PCB headers           |
| Product family            | PCV 5/...-GF          |
| Product line              | COMBICON Connectors L |
| Number of positions       | 6                     |
| Pitch                     | 15.24 mm              |
| Number of rows            | 1                     |
| Pin layout                | Linear pinning        |
| Solder pins per potential | 3                     |

### Electrical properties

#### Properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 32 A   |
| Nominal voltage $U_N$       | 1000 V |
| Contact resistance          | 0.5 mΩ |
| Rated voltage (III/3)       | 1000 V |
| Rated surge voltage (III/3) | 8 kV   |
| Rated voltage (III/2)       | 1000 V |
| Rated surge voltage (III/2) | 8 kV   |
| Rated voltage (II/2)        | 1000 V |
| Rated surge voltage (II/2)  | 6 kV   |

### Mounting

|               |                |
|---------------|----------------|
| Mounting type | Wave soldering |
| Pin layout    | Linear pinning |

#### Flange

|                   |                   |
|-------------------|-------------------|
| Tightening torque | 0.3 Nm ... 0.7 Nm |
|-------------------|-------------------|

#### Attachment on the PCB

|                   |                      |
|-------------------|----------------------|
| Tightening torque | 0.3 Nm               |
| Screw             | 1705449 DFK-PC 16-SS |

### Material specifications

#### Material data - contact

|                                          |                                                                                  |
|------------------------------------------|----------------------------------------------------------------------------------|
| Note                                     | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                         | Cu alloy                                                                         |
| Surface characteristics                  | hot-dip tin-plated                                                               |
| Metal surface contact area (top layer)   | Tin (4 - 8 μm Sn)                                                                |
| Metal surface soldering area (top layer) | Tin (4 - 8 μm Sn)                                                                |

# PCV 5/ 6-GF-15,24 - PCB header

1392190

<https://www.phoenixcontact.com/us/products/1392190>

## Material data - housing

|                                                                   |              |
|-------------------------------------------------------------------|--------------|
| Color (Housing)                                                   | green (6021) |
| Insulating material                                               | PA           |
| Insulating material group                                         | I            |
| CTI according to IEC 60112                                        | 600          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C       |

## Notes

|                    |                                                                                                                                                                                          |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | In accordance with IEC 61984, COMBICON connectors have no switching power (COC). During designated use, they must not be plugged in or disconnected when carrying voltage or under load. |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Dimensions

|                       |                                                                                      |
|-----------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing   |  |
| Pitch                 | 15.24 mm                                                                             |
| Width [w]             | 99.92 mm                                                                             |
| Height [h]            | 34.25 mm                                                                             |
| Length [l]            | 13.54 mm                                                                             |
| Installed height      | 29.25 mm                                                                             |
| Solder pin length [P] | 5 mm                                                                                 |
| Pin dimensions        | 0.8 x 1 mm                                                                           |

## PCB design

|               |        |
|---------------|--------|
| Hole diameter | 1.3 mm |
|---------------|--------|

## Mechanical tests

### Visual inspection

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-1:2002-02 |
| Result        | Test passed           |

### Dimension check

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-2:2002-02 |
| Result        | Test passed           |

### Resistance of inscriptions

|               |                        |
|---------------|------------------------|
| Specification | IEC 60068-2-70:1995-12 |
|---------------|------------------------|

# PCV 5/ 6-GF-15,24 - PCB header



1392190

<https://www.phoenixcontact.com/us/products/1392190>

|                                                |                        |
|------------------------------------------------|------------------------|
| Result                                         | Test passed            |
| Polarization and coding                        |                        |
| Specification                                  | IEC 60512-13-5:2006-02 |
| Result                                         | Test passed            |
| Contact holder in insert                       |                        |
| Specification                                  | IEC 60512-15-1:2008-05 |
| Contact holder in insert<br>Requirements >20 N | Test passed            |
| Insertion and withdrawal forces                |                        |
| Result                                         | Test passed            |
| No. of cycles                                  | 25                     |
| Insertion strength per pos. approx.            | 9 N                    |
| Withdraw strength per pos. approx.             | 5 N                    |

## Electrical tests

### Thermal test | Test group C

|                            |                       |
|----------------------------|-----------------------|
| Specification              | IEC 60512-5-1:2002-02 |
| Tested number of positions | 12                    |

### Insulation resistance

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | > 5 MΩ                |

### Air clearances and creepage distances | 1. Insulation coordination

|                                                        |                   |
|--------------------------------------------------------|-------------------|
| Specification                                          | IEC 61984:2008-10 |
| Insulating material group                              | I                 |
| Comparative tracking index (IEC 60112)                 | CTI 600           |
| Rated insulation voltage (III/3)                       | 1000 V            |
| Rated surge voltage (III/3)                            | 8 kV              |
| minimum clearance value - non-homogenous field (III/3) | 8 mm              |
| minimum creepage distance (III/3)                      | 12.5 mm           |
| Rated insulation voltage (III/2)                       | 1000 V            |
| Rated surge voltage (III/2)                            | 8 kV              |
| minimum clearance value - non-homogenous field (III/2) | 8 mm              |
| minimum creepage distance (III/2)                      | 8 mm              |
| Rated insulation voltage (II/2)                        | 1000 V            |
| Rated surge voltage (II/2)                             | 6 kV              |
| minimum clearance value - non-homogenous field (II/2)  | 5.5 mm            |
| minimum creepage distance (II/2)                       | 5.5 mm            |

### Air clearances and creepage distances | 2. Insulation coordination

|                                        |                     |
|----------------------------------------|---------------------|
| Specification                          | IEC 60664-1:2007-04 |
| Insulating material group              | I                   |
| Comparative tracking index (IEC 60112) | CTI 600             |

# PCV 5/ 6-GF-15,24 - PCB header



1392190

<https://www.phoenixcontact.com/us/products/1392190>

|                                                        |           |
|--------------------------------------------------------|-----------|
| Rated insulation voltage (III/3)                       | 1250 V DC |
| Rated surge voltage (III/3)                            | 8 kV      |
| minimum clearance value - non-homogenous field (III/3) | 8 mm      |
| minimum creepage distance (III/3)                      | 16 mm     |
| Rated insulation voltage (III/2)                       | 1500 V DC |
| Rated surge voltage (III/2)                            | 10 kV     |
| minimum clearance value - non-homogenous field (III/2) | 11 mm     |
| minimum creepage distance (III/2)                      | 11 mm     |
| Rated insulation voltage (II/2)                        | 1500 V DC |
| Rated surge voltage (II/2)                             | 8 kV      |
| minimum clearance value - non-homogenous field (II/2)  | 8 mm      |
| minimum creepage distance (II/2)                       | 8 mm      |

## Environmental and real-life conditions

### Vibration test

|                        |                             |
|------------------------|-----------------------------|
| Specification          | IEC 60068-2-6:2007-12       |
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz) |
| Acceleration           | 5g (60.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |
| Test directions        | X-, Y- and Z-axis           |

### Durability test

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-9-1:2010-03 |
| Impulse withstand voltage at sea level       | 7.3 kV                |
| Contact resistance R <sub>1</sub>            | 0.5 mΩ                |
| Contact resistance R <sub>2</sub>            | 0.5 mΩ                |
| Insertion/withdrawal cycles                  | 25                    |
| Insulation resistance, neighboring positions | > 5 MΩ                |

### Climatic test

|                                   |                                                                           |
|-----------------------------------|---------------------------------------------------------------------------|
| Specification                     | ISO 6988:1985-02                                                          |
| Corrosive stress                  | 0.2 dm <sup>3</sup> SO <sub>2</sub> on 300 dm <sup>3</sup> /40 °C/1 cycle |
| Thermal stress                    | 105 °C/168 h                                                              |
| Power-frequency withstand voltage | 3.31 kV                                                                   |

### Ambient conditions


|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 105 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Packaging specifications

|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|

## Drawings

Diagram



Type: PC 5/...-STF1-15,24 with PCV 5/...-GF-15,24

# PCV 5/ 6-GF-15,24 - PCB header



1392190

<https://www.phoenixcontact.com/us/products/1392190>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1392190>

|  <b>cULus Recognized</b><br>Approval ID: E60425-19920722 |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                           | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                                         |                       |                       |                   |                             |
|                                                                                                                                           | 300 V                 | 41 A                  | -                 | -                           |
| D                                                                                                                                         |                       |                       |                   |                             |
|                                                                                                                                           | 600 V                 | 5 A                   | -                 | -                           |

|  <b>UL Recognized</b><br>Approval ID: E60425-19920722 |                       |                       |                   |                             |
|----------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                        | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| F                                                                                                                                      |                       |                       |                   |                             |
|                                                                                                                                        | 1000 V                | 41 A                  | -                 | -                           |
| C                                                                                                                                      |                       |                       |                   |                             |
|                                                                                                                                        | 150 V                 | 41 A                  | -                 | -                           |

|  <b>cUL Recognized</b><br>Approval ID: E60425-19920722 |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                           | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| C                                                                                                                                         |                       |                       |                   |                             |
|                                                                                                                                           | 1000 V                | 41 A                  | -                 | -                           |

# PCV 5/ 6-GF-15,24 - PCB header



1392190

<https://www.phoenixcontact.com/us/products/1392190>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002637 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PCV 5/ 6-GF-15,24 - PCB header



1392190

<https://www.phoenixcontact.com/us/products/1392190>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)