

PACT MCR-V2-4012- 70- 250-5A-1 - Current transformer



2277116

<https://www.phoenixcontact.com/us/products/2277116>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Window-type current transformer, 250 A AC primary current; 5 A AC secondary current; accuracy class 1; 5 VA rated power

Commercial data

Item number	2277116
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C444
Product key	CMMA11
GTIN	4046356305082
Weight per piece (including packing)	385 g
Weight per piece (excluding packing)	299 g
Customs tariff number	85043129
Country of origin	DE

PACT MCR-V2-4012- 70- 250-5A-1 - Current transformer



2277116

<https://www.phoenixcontact.com/us/products/2277116>

Technical data

Product properties

Product type	Current transformer
--------------	---------------------

Electrical properties

Rated insulation voltage	1 kV (Phase/neutral conductor)
--------------------------	--------------------------------

General

Can be calibrated	no
Converter type	Window-type current transformer

Input data

Current transformer

Rated power	5 VA
Thermal rated short-time current	$I_{th} = 60 * I_n$
Thermal rated continuous current	$I_d = 1.2 * I_n$
Rated surge current	$I_{dyn} = 2.5 * I_{th}$
Rated frequency f_n	50 Hz
	60 Hz
Primary rated current I_{pn}	0 A AC ... 250 A AC
Can be calibrated	no
Converter type	Window-type current transformer

Output data

Signal

Designation	Current output
Secondary rated current I_{sn}	5 A AC
Surge current limitation factor	FS 5
Accuracy class	1

Connection data

Connection method	Screw connection
Stripping length	10 mm
Conductor cross-section flexible	2x 10 mm ² ... 10 mm ² (Secondary terminals)
Tightening torque	2 Nm ... 2 Nm

Dimensions

Item dimensions

Width	31 mm
Height	92 mm
Depth	70 mm

PACT MCR-V2-4012- 70- 250-5A-1 - Current transformer



2277116

<https://www.phoenixcontact.com/us/products/2277116>

Item dimensions with alternative mounting

Width	70 mm
Height	92 mm
Depth	31 mm

Copper rail

Width	40 mm
Height	12 mm

Copper rail 2

Width	30 mm
Height	10 mm

Circular conductor

Diameter	33 mm
----------	-------

Drill hole

Diameter	6.5 mm
----------	--------

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0 (Housing)
Housing material	PA 6.6

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 40 °C
Ambient temperature (storage/transport)	-25 °C ... 40 °C
Altitude	≤ 1000 m
Permissible humidity (operation)	Use only indoors, non-condensing
Insulating material class	H

Approvals

CE

Certificate	CE-compliant
-------------	--------------

UKCA

Certificate	UKCA-compliant
-------------	----------------

UL, USA/Canada

Identification	XODW8.E323953
----------------	---------------

Standards and regulations

Standards/regulations	EN 61869
-----------------------	----------

Mounting

PACT MCR-V2-4012- 70- 250-5A-1 - Current transformer



2277116
<https://www.phoenixcontact.com/us/products/2277116>

Mounting type	DIN rail mounting
	Panel mounting

PACT MCR-V2-4012- 70- 250-5A-1 - Current transformer




2277116

<https://www.phoenixcontact.com/us/products/2277116>

Drawings

Dimensional drawing



PACT MCR-V2-4012- 70- 250-5A-1 - Current transformer



2277116

<https://www.phoenixcontact.com/us/products/2277116>

Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2277116>



EAC

Approval ID: RU*DE*08.B.01187/19



cULus Recognized

Approval ID: E323953

PACT MCR-V2-4012- 70- 250-5A-1 - Current transformer



2277116
<https://www.phoenixcontact.com/us/products/2277116>

Classifications

ECLASS

ECLASS-13.0	27210902
ECLASS-15.0	27210902

ETIM

ETIM 9.0	EC002048
----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

2277116
<https://www.phoenixcontact.com/us/products/2277116>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com