


2298331

<https://www.phoenixcontact.com/us/products/2298331>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE module, with COMBICON connectors and two potentials (+ -) for potential distribution, for mounting on NS 35/7.5 or NS 32



Commercial data

Item number	2298331
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C429
Product key	DK2A84
GTIN	4017918587789
Weight per piece (including packing)	59.6 g
Weight per piece (excluding packing)	61.4 g
Customs tariff number	85369010
Country of origin	DE

Technical data

Notes

Notes on operation	The necessary requirements for insulation (basic insulation or reinforced insulation) from adjacent modules (in DIN-rail direction) must be realized by applying suitable measures (e. g., partition plates).
Notes on operation	Ensure that the supply voltage of the device has a common reference potential.
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

Product properties

Product type	Potential distributor
Product family	VARIOFACE

Insulation characteristics

Insulation	Functional insulation
Pollution degree	2

Electrical properties

Nominal voltage U_N	230 V AC/DC
Max. total current of all branches	12 A
Rated insulation voltage	230 V
Rated surge voltage	2.1 kV (1.2/50 μ s)

Connection data

Feed-in

Number of connections	2
Pitch	5.08 mm

Distribution

Number of connections	12
-----------------------	----

Dimensions

Width	25 mm
Height	97 mm
Depth	42 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	\geq IP54 (Installation location)

UM 25-PVB 2/12ICV/SO19 - Potential distributors



2298331

<https://www.phoenixcontact.com/us/products/2298331>

Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	≤ 2000 m

Standards and regulations

Standards/regulations	EN 60664-1
-----------------------	------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

UM 25-PVB 2/12ICV/SO19 - Potential distributors



2298331

<https://www.phoenixcontact.com/us/products/2298331>

Classifications

ECLASS

ECLASS-13.0	27400609
ECLASS-15.0	27400609

ETIM

ETIM 9.0	EC001894
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UM 25-PVB 2/12ICV/SO19 - Potential distributors



2298331
<https://www.phoenixcontact.com/us/products/2298331>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com